

P	LTR	DESCRIPTION	DATE	DWN	APVD
	10	INITIAL RELEASE	11FEB2020	GK	AK

NOTES: —

1. CHARACTERS: —


0–9, A–Z, +, –, /,~, ≡
0, 1, 6 & 9 FOLLOWED BY A FULL STOP.
HEIGHT 2.6 – 2.9 mm
TOLERANCE (AXIAL) ±0.75
(ROTATIONAL) ±5°

CHEVRON CUT MARKERS: —


CHARACTERS TO BE CENTRALLY DISPOSED
ON MARKER FACE AND IN THE ATTITUDE
SHOWN RELATIVE TO CHEVRON.

2. MARKER LENGTHS (DIMENSION 'A') : —


WITH SINGLE MARK 4.00–4.75
WITH DOUBLE MARK 6.75–7.25



CHEVRON CUT



STRAIGHT CUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GOPALAKRISHNA H V 11FEB2020	 TE Connectivity		
		CHK ALAN KEAN 11FEB2020			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD ALAN KEAN 11FEB2020	NAME MARKER Z TYPE SIZE 18 STRAIGHT / CHEVRON CUT		
	0 PLC ± – 1 PLC ± 0.2 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –	PRODUCT SPEC —	SIZE A3		
MATERIAL PVC 6.12 – 5.54g/250mm	FINISH —	APPLICATION SPEC —	CAGE CODE 00779	DRAWING NO C-1601A0007	RESTRICTED TO —
		WEIGHT —	CUSTOMER DRAWING		
		SCALE 10:1		SHEET 1 OF 1	REV 10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EJ2247-000](#)