

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2020 TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

| P | LTR | DESCRIPTION              | DATE      | DWN | APVD |
|---|-----|--------------------------|-----------|-----|------|
|   | 9   | INITIAL CUSTOMER DRAWING | 10FEB2020 | AFK | LS   |

NOTES:-

1. CHARACTERS:-  
0-9, A-Z, +, -, /, ~ & ±  
0, 1, 6 & 9 ARE FOLLOWED BY A FULL STOP  
TOLERANCE (AXIAL) ±0.75  
(ROTATIONAL) ±5°

The drawing shows two views of a marker. The left view is an end view showing an elliptical shape with dimensions: 'A' for height, 'B' for width, and 'T' for thickness. The right view is a side view showing a rectangular shape with dimensions: 'L' for length and 'C' for height. The height 'C' is also labeled as 'nom.' (nominal). The marker has a stepped profile on the right side.

| DESCRIPTION<br>(1st 4 DIGITS) | SIZE | "A"         | "B"         | CHARACTER<br>HEIGHT "C" | "L"         | "T"         | WEIGHT /<br>250mm |
|-------------------------------|------|-------------|-------------|-------------------------|-------------|-------------|-------------------|
| 1358                          | 30   | 4.95 – 5.25 | 1.30 – 1.60 | 2.4                     | 4.25 – 4.75 | 0.68 – 0.78 | 2.94 – 3.24       |
| 1361                          | 65   | 9.90 – 10.2 | 2.90 – 3.20 | 4.0                     | 5.50 – 6.00 | 1.18 – 1.28 | 9.57 – 10.57      |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL  
PVC

DWN  
AFK

CHK  
-

APVD  
-

PRODUCT SPEC  
RW-2535

APPLICATION SPEC  
-

WEIGHT  
SEE TABLE

CUSTOMER DRAWING

07FEB2020

TE Connectivity

NAME  
MARKER, K TYPE

SIZE  
A3

CAGE CODE  
0198G

DRAWING NO  
C-1602A0001

RESTRICTED TO  
-

SCALE  
-

SHEET  
1 OF 1

REV  
9

1470-19 (1/15)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EC6545-000](#)