





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		P	REVISED PER ECO-11-005027	18MAR2011	RK	HMR
			P1	REV PER ECR-11-023441	17NOV2011	AY	SZ
			P2	REVISED PER ECR-15-013928	22SEP2015	RS	SZ

D



(P2) PART NUMBER: 1604037-1

C



THIS PRODUCT HAS PASSED VERIFICATION AND AGENCY APPROVALS TESTING AND IS COMPONENT RECOGNIZED PER UL 1977 AND CSA 22.2. TE CONNECTIVITY PRODUCT QUALIFICATION TESTING IS NOT YET COMPLETED.

BLACK	1604037-6
BLUE	1604037-5
GRAY	1604037-4
RED	1604037-3
ORANGE	1604037-2
YELLOW	1604037-1
HOUSING COLOR	ASSEMBLY PART NO

B

A

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.D. YOHN CHK W. BERNHART APVD J.A. FULPONT		12DEC2001 12DEC2001 12DEC2001		 TE Connectivity					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		SUB-ASSY, HOUSING W/ SPRING, AMP POWER SERIES 175					
		0 PLC ±0.13 1 PLC ±0.13 2 PLC ±0.13 3 PLC ±0.13 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A200779		DRAWING NO C-1604037		RESTRICTED TO -	
MATERIAL -		-		CUSTOMER DRAWING		SCALE 2:1		SHEET 1 OF 2		REV P2	


D

C


B

A


LOC	DIST	REVISIONS					
CM	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-




P2 PART NUMBER: 1604037-2




P2 PART NUMBER: 1604037-3




P2 PART NUMBER: 1604037-4



P2 PART NUMBER: 1604037-5



P2 PART NUMBER: 1604037-6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.D.YOHN 12DEC2001	 TE Connectivity			
DIMENSIONS:		CHK W.BERNHART 12DEC2001				
mm		APVD J.A.FULPONT 12DEC2001	NAME SUB-ASSY, HOUSING W/ SPRING, AMP POWER SERIES 175			
		PRODUCT SPEC	SIZE		CAGE CODE	DRAWING NO
		APPLICATION SPEC	A200779		C=1604037	RESTRICTED TO
MATERIAL		WEIGHT	SCALE		SHEET	OF
-		-	2:1		2	2
		CUSTOMER DRAWING			REV	P2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1604037-3](#)