



LOC	DIST	REVISIONS				
CM	0	P	LTR	DESCRIPTION	DATE	APVD
		B		OBSOLETE PER ECO-18-010313	26JUN2019	SZ
		BI		REACTIVATE PN-1	20DEC2019	SZ

THIS PRODUCT HAS PASSED VERIFICATION AND AGENCY APPROVALS TESTING AND IS COMPONENT RECOGNIZED PER UL 1977 AND CSA 22.2. TYCO ELECTRONICS PRODUCT QUALIFICATION TESTING IS NOT YET COMPLETE.



NOTES:
1. MATERIAL: HIGH CONDUCTIVE COPPER ALLOY.



METRIC

OBSOLETE

TIN	1604113-2
SILVER	1604113-1
FINISH	PART NUMBER

DIMENSIONS: mm		DWN B. HAYMAKER 11APR2002	MATERIAL -		FINISH -
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±0.5 2 PLC ±0.30 3 PLC ±0.150 4 PLC ± ANGLES ±5°		CHK K. KETELSLEGER 11APR2002	 Tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608		
		APVD K. KETELSLEGER 11APR2002			
		PRODUCT SPEC 108-2149	NAME AMP POWER 15 CONTACT CRIMPED WITH 16/18/20 AWG		
		APPLICATION SPEC 114-13127	SIZE A4	CAGE CODE 00779	DRAWING NO C-1604113
		WEIGHT -	RESTRICTED TO		
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1	OF 1
				REV BI	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1604113-1](#)