



DIMENSIONS IN **m.m.** --DO NOT SCALE PRINT

NUMBER
C-160597-E

P	LTR REV	REVISION RECORD MODIFICATIONS	DATE	DWN DESS	APVD VER
	D1	REVISED PER ECO-09-026346	25NOV09	KK	AEG



3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



3 OBSOLETE

ORDER NO.	FINISH	REMARKS
160597-1	NONE	1
160597-3	SILVER- "	1
160597-4	TIN-PLATED	2
160597-5	GOLD-PLATED	1

- 1 FOR USE ON STANDARD APPLICATIONS
(RIGHT-LEFT FEED)
- 2 FOR USE ON MINIATURE APPLICATIONS
(LEFT-RIGHT FEED) AMP-O-MATOR APPLICATION

CUSTOMER PRINT
FOR REFERENCE ONLY

© 1966 BY AMP HOLLAND NV. ALL
RIGHTS RESERVED AMP PRODUCTS
COVERED BY PATENTS AND/OR PAT-
ENTS PENDING

-9	-8	-7	-6	-5	-4	-3	-2	-1	DWG SIZE	NUMBER	NAME	REMARKS	ITEM NO.
REQUIRED PER ASSEMBLY									MATERIAL	HEAT TREAT	FINISH		
									BRASS		SEE TABLE		
									AMP	DR. H/ISSER. 2-JAN-66	DATE APP. 10/1/66	DATE	
									AMP-HOLLAND N.V.	TYPE	PRINT DIST	LOC	
									1-HERTOGENBOSCH	A.M.			
									HOLLAND				
									SCALE	WIRE SIZE	CMA	NAME	
									4-1	0.05-0.15	MAX		
									mm	MIN			
									"110 BER" PISTON RECEPTACLE				
									C-160597-E				
									D1				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[160597-4](#)