



E-311AAB REV. C

REVISIONS		RELEASED	86-08-20
REV.	DESCRIPTION	DATE	APPROVED
C	0632-03 REDRAWN; ADDED ITEM 6	03/07/15	CC




SCHEMATIC No. 32340-001

TIME ——— VOLTAGE CURVE				
SPEC. MIL - STD - 704C				
VOLTAGE	MIN.	TIME	MAX.	TIME
32.5		.075		.30
35.0		.062		.16
40		.046		.091
45		.029		.061
50		.012		.045

TRIP POINT
CONTACT RATING
CONTACT ARRANGEMENT
OPERATE TEMPERATURES
WEIGHT MAX.
MAX. VOLTAGE
CONSTRUCTION

31.5 ±1 VDC
5 AMP RES
SPST N.C.
-55°C TO +71°C
6 OZ.
150 V.
CONTACTS HERMETICALLY SEALED



6	2	39529-001	OVERLAY			
5	1	30326-020	RELAY ASSEMBLY-PRIMARY			
4	4	51806-014	WASHER-LOCK-No. 6 SPLIT			BRONZE
3	4	50406-034	NUT-No. 6-32 X 1/4 X5/64 HEX.			BRASS
2	1	32743-001	PLATE-WIRING DIAGRAM			
1	1	22039-001	PLATE-NAME			
FIND NO	QTY REQD	PART OR IDENTIFYING NO	NOMENCLATURE OR DESCRIPTION	FSC NO	DRAWING OR SPECIFICATION	MATERIAL OR NOTE
			TYCO Electronics Hartman Division, 175 N. DIAMOND STREET, WANSFELD, OHIO 44902			
			DR BY: CSC 03/08/21 CHK BY: CC 03/08/27 ENGR: LST 03-08-27 MFG: MB 03-08-27	RELAY - OVERVOLTAGE WITH TIME DELAY 093		
			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON	DRG NO. E-311AAB		
			2 PL DEC. 3 PL DEC. ANGLES ± .03 .010 ± 1°	REF TYCO P/N 0-1616126-8		
			SIZE C 74063	SCALE NINE SHEET		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1616126-8](#)