



# FAA/PMA



REVISIONS			REV.
REV.	DESCRIPTION	DATE	APPROVED
H	40471 REDRAWN, *MAX* ADDED TO .59	99/09/27	RS
J	41485 *MAX* ADDED TO .76 & 1.03	00/02/01	RS



.166 DIA HOLE, C-BORE  
.265 DIA X .12 DEEP  
2 MTG HOLES



**OPERATE CHARACTERISTICS**  
CONTINUOUS 6.25 AMPS DC MAX  
PICKUP 3.5 AMPS DC MAX  
DROPOUT 1.4 AMP MIN.  
CONTACT RATING .25 AMP 28 VDC  
LAMP LOAD .080 AMP 28 VDC  
VIBRATION 10 G'S TO 500 HZ  
ALTITUDE 60,000 FT. MAX  
TEMP. -55°C TO +71°C  
MAX. WEIGHT 1.25 OZ.



6-32 UNC-2A  
5 REQ'D.

PART NO.  
OPERATE AMPS  
SERIAL NO.  
HARTMAN ELEC. MFG.

QTY	PART OR IDENTIFYING NO	INDICATOR OR DESCRIPTION	FSO#	DRAWING OR SPECIFICATION	MATERIAL OR NOTE
6	39529-024	OVERLAY			
5	58400-173	PLATE - FAA/PMA			
4	51806-014	WASHER - LOCK NO.6 SPLIT			BRONZE
3	50406-034	NUT - 6-32 X 1/4 X 5/64 HEX			BRASS
2	35893-020	RELAY ASSEMBLY - PRIMARY			
1	34246-001	PLATE - NAME			

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES IN			HARTMAN ELECTRICAL MANUFACTURING MANASSALET, OHIO		
2 PL. DEC. .13	PL. DEC. .10	PL. DEC. .10	DR BY RLS	00/02/25	RELAY - CURRENT INDICATOR
*.06	*.010	*.1*	CHK BY KRS	00/02/25	SIZE C
MATERIAL	ENG BY RAB	00/03/03	RELEASE		CODE IDENT 74063
	MFG	00/03/03	CONTR NO.		DWG NO. Q-50E
	GOVT APPVL				SCALE NONE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1616131-8](#) [1616540-1](#)