


- 1 APPLIES FROM EDGE OF METAL WIRE BARREL
TO CENTER OF STUD HOLE
- 2 MATERIAL:
BODY & SLEEVE: COPPER PER ASTM B152
INSULATION: NYLON
- 3 FINISH:
BODY & SLEEVE: TIN PLATED PER ASTM B545
INSULATION: COLOR — YELLOW
- 4 STAMP AMP 12-10* APPROX AS SHOWN
- 5 FOR 3.810 TO 6.350[.150 TO .250]
INS. DIA



500	LOOSE PIECE	165034
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	07JUN2018
RAVI S	
CHK	07JUN2018
ROHDE DANIEL F	
APVD	07JUN2018
ROHDE DANIEL F	
PRODUCT SPEC	
UL 486 A-B	
APPLICATION SPEC	
114-2157	
WEIGHT	



TE Connectivity Ltd.

8	NAME	TERMINAL, RING TONGUE, PIDG WIRE SIZE: 12-10 AWG
---	------	--

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:	105°C[221°F]
--	--------------

VOLTAGE RATING:
300 V MAX

WIRE CROSS SECTIONAL AREA RANGE,
2.62-6.64mm²[5,180-13,100] CIR MILS

DIMENSIONS:
mm [INCHES]



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0	PLC	$\pm -$
1	PLC	$\pm -$
2	PLC	$\pm -$
3	PLC	$\pm 0.127[.005]$
4	PLC	$\pm -$
ANGLES		$\pm -$
FINISH		$\pm -$

	MATERIAL
--	----------

3

CUSTOMER DRAWING

SCALE N.T.S.

SHEET 1 OF 1

REV B1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-165034-1](#)