




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APPD
	N	REVISED PER ECR-19-008349	29MAY2019	AL	HL


- | | |
|---|--|
|  | HOUSING: LCP, BLACK.
CONTACT & GROUND PLANE: PHOS BRONZE. |
|  | CONTACT PLATING: SELECT 0.25 MICROMETERS (.00010 IN)
MIN. GOLD. |
|  | FOR STANDARD APPLICATIONS, ORIENTATION HOLE TO BE
ø1.02 [ø.0400]. |
|  | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |



SECTION A-A



DIFFERENTIAL PAIR LOADING
(BOTTOM VIEW)
SCALE 2:1



RECOMMENDED PC BOARD LAYOUT
(VIEWED FROM CONNECTOR SIDE)

26.99(1.063)	40.00(1.575)	2	0.152(0.060)	60.13(2.368)	55.20(2.173)	61.28(2.412)	YES	POCKET TAPE	YES	84	7-16580(12)
16.98(669)	20.00(.7874)	1	0.102(0.040)	40.13(1.580)	35.20(1.386)	41.28(1.625)	YES	POCKET TAPE	YES	56	7-16580(12)
6.99(275)	0(.000)	0	0.102(0.040)	20.13(.793)	15.20(.598)	21.29(.838)	YES	POCKET TAPE	YES	28	7-16580(12)
26.99(1.063)	40.00(1.575)	2	0.152(0.060)	60.13(2.368)	55.20(2.173)	61.28(2.412)	YES	POCKET TAPE	YES	84	7-16580(12)
16.98(669)	20.00(.7874)	1	0.102(0.040)	40.13(1.580)	35.20(1.386)	41.28(1.625)	YES	POCKET TAPE	NO	80	6-16580(12)
6.99(275)	0(.000)	0	0.102(0.040)	20.13(.793)	15.20(.598)	21.29(.838)	YES	POCKET TAPE	NO	40	6-16580(12)
40.00(1.575)	0(.000)	0	0.152(0.060)	60.13(2.368)	55.20(2.173)	61.28(2.412)	YES	POCKET TAPE	NO	120	6-16580(12)
-	20.00(.7874)	1	0.102(0.040)	40.13(1.580)	35.20(1.386)	41.28(1.625)	NO	POCKET TAPE	YES	56	5-16580(12)
-	0(.000)	0	0.102(0.040)	20.13(.793)	15.20(.598)	21.29(.838)	NO	POCKET TAPE	YES	28	5-16580(12)
-	40.00(1.575)	2	0.152(0.060)	60.13(2.368)	55.20(2.173)	61.28(2.412)	NO	POCKET TAPE	NO	120	4-16580(12)
40.00(1.575)	0(.000)	0	0.152(0.060)	60.13(2.368)	55.20(2.173)	61.28(2.412)	NO	POCKET TAPE	NO	120	4-16580(12)
-	0(.000)	0	0.102(0.040)	20.13(.793)	15.20(.598)	21.29(.838)	NO	POCKET TAPE	NO	40	4-16580(12)
47.00(1.850)	60.00(3.150)	4	0.152(0.060)	100.14(3.943)	95.20(3.749)	101.30(3.988)	YES	TRAY	YES	140	3-16580(12)
36.99(1.456)	40.00(1.575)	3	0.102(0.040)	60.13(2.368)	55.20(2.173)	61.28(2.412)	YES	TRAY	YES	140	3-16580(12)
26.99(1.063)	40.00(1.575)	2	0.152(0.060)	60.13(2.368)	55.20(2.173)	61.28(2.412)	YES	TRAY	YES	84	3-16580(12)
16.98(669)	20.00(.7874)	1	0.102(0.040)	40.13(1.580)	35.20(1.386)	41.28(1.625)	YES	TRAY	YES	56	3-16580(12)
6.99(275)	0(.000)	0	0.102(0.040)	20.13(.793)	15.20(.598)	21.29(.838)	YES	TRAY	YES	28	3-16580(12)
47.00(1.850)	60.00(3.150)	4	0.152(0.060)	100.14(3.943)	95.20(3.749)	101.30(3.988)	YES	TRAY	NO	200	2-16580(12)
36.99(1.456)	60.00(3.150)	3	0.152(0.060)	100.14(3.155)	75.20(2.961)	81.28(3.200)	YES	TRAY	NO	160	2-16580(12)
26.99(1.063)	40.00(1.575)	2	0.152(0.060)	60.13(2.368)	55.20(2.173)	61.28(2.412)	YES	TRAY	NO	120	2-16580(12)
16.98(669)	20.00(.7874)	1	0.102(0.040)	40.13(1.580)	35.20(1.386)	41.28(1.625)	YES	TRAY	NO	80	2-16580(12)
6.99(275)	0(.000)	0	0.102(0.040)	20.13(.793)	15.20(.598)	21.29(.838)	YES	TRAY	NO	40	2-16580(12)
-	60.00(3.150)	4	0.152(0.060)	100.14(3.943)	95.20(3.749)	101.30(3.988)	NO	TRAY	YES	140	1-16580(12)
-	60.00(3.150)	3	0.152(0.060)	100.14(3.155)	75.20(2.961)	81.28(3.200)	NO	TRAY	YES	140	1-16580(12)
-	40.00(1.575)	2	0.152(0.060)	60.13(2.368)	55.20(2.173)	61.28(2.412)	NO	TRAY	YES	84	1-16580(12)
-	20.00(.7874)	1	0.102(0.040)	40.13(1.580)	35.20(1.386)	41.28(1.625)	NO	TRAY	YES	56	1-16580(12)
-	0(.000)	0	0.102(0.040)	20.13(.793)	15.20(.598)	21.29(.838)	NO	TRAY	YES	28	1-16580(12)
-	60.00(3.150)	4	0.152(0.060)	100.14(3.943)	95.20(3.749)	101.30(3.988)	NO	TRAY	NO	200	1-16580(12)
-	60.00(3.150)	3	0.152(0.060)	100.14(3.155)	75.20(2.961)	81.28(3.200)	NO	TRAY	NO	160	1-16580(12)
-	40.00(1.575)	2	0.152(0.060)	60.13(2.368)	55.20(2.173)	61.28(2.412)	NO	TRAY	NO	120	1-16580(12)
-	20.00(.7874)	1	0.102(0.040)	40.13(1.580)	35.20(1.386)	41.28(1.625)	NO	TRAY	NO	80	1-16580(12)
-	0(.000)	0	0.102(0.040)	20.13(.793)	15.20(.598)	21.29(.838)	NO	TRAY	NO	40	1-16580(12)
G	F	D					POLYIMIDE	PACKAGING	DIFF.	NO OF	PART
							TYPE				NUMBER

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1658012-3](#)