




4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

## REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
| - | -   | SEE SHEET 1 | -    | -   | -    |



|              |              |   |              |              |              |               |                      |                |            |           |             |
|--------------|--------------|---|--------------|--------------|--------------|---------------|----------------------|----------------|------------|-----------|-------------|
| 27.01(1.063) | 40.00(1.575) | 2 | 0.102(.0040) | 58.50(2.303) | 55.20(2.173) | 60.00(2.362)  | YES                  | POCKET TAPE    | YES        | 84        | 7-1658044-3 |
| 17.00(.669)  | 20.00(.7874) | 1 | 0.102(.0040) | 38.48(1.515) | 35.20(1.386) | 40.00(1.575)  | YES                  | POCKET TAPE    | YES        | 56        | 7-1658044-2 |
| 6.99(.275)   | 0(.000)      | 0 | 0.102(.0040) | 18.49(.728)  | 15.20(.598)  | 20.00(.787)   | YES                  | POCKET TAPE    | YES        | 28        | 7-1658044-1 |
| 27.01(1.063) | 40.00(1.575) | 2 | 0.102(.0040) | 58.50(2.303) | 55.20(2.173) | 60.00(2.362)  | YES                  | POCKET TAPE    | NO         | 120       | 6-1658044-3 |
| 17.00(.669)  | 20.00(.7874) | 1 | 0.102(.0040) | 38.48(1.515) | 35.20(1.386) | 40.00(1.575)  | YES                  | POCKET TAPE    | NO         | 80        | 6-1658044-2 |
| 6.99(.275)   | 0(.000)      | 0 | 0.102(.0040) | 18.49(.728)  | 15.20(.598)  | 20.00(.787)   | YES                  | POCKET TAPE    | NO         | 40        | 6-1658044-1 |
| -            | 40.00(1.575) | 2 | 0.102(.0040) | 58.50(2.303) | 55.20(2.173) | 60.00(2.362)  | NO                   | POCKET TAPE    | YES        | 84        | 5-1658044-3 |
| -            | 20.00(.7874) | 1 | 0.102(.0040) | 38.48(1.515) | 35.20(1.386) | 40.00(1.575)  | NO                   | POCKET TAPE    | YES        | 56        | 5-1658044-2 |
| -            | 0(.000)      | 0 | 0.102(.0040) | 18.49(.728)  | 15.20(.598)  | 20.00(.787)   | NO                   | POCKET TAPE    | YES        | 28        | 5-1658044-1 |
| -            | 40.00(1.575) | 2 | 0.102(.0040) | 58.50(2.303) | 55.20(2.173) | 60.00(2.362)  | NO                   | POCKET TAPE    | NO         | 120       | 4-1658044-3 |
| -            | 20.00(.7874) | 1 | 0.102(.0040) | 38.48(1.515) | 35.20(1.386) | 40.00(1.575)  | NO                   | POCKET TAPE    | NO         | 80        | 4-1658044-2 |
| -            | 0(.000)      | 0 | 0.102(.0040) | 18.49(.728)  | 15.20(.598)  | 20.00(.787)   | NO                   | POCKET TAPE    | NO         | 40        | 4-1658044-1 |
| 47.00(1.850) | 80.00(3.150) | 4 | 0.152(.0060) | 98.50(3.748) | 95.20(3.748) | 100.00(3.937) | YES                  | TRAY           | YES        | 140       | 3-1658044-5 |
| 37.02(1.457) | 60.00(2.362) | 3 | 0.152(.0060) | 78.49(3.090) | 75.20(2.961) | 80.00(3.150)  | YES                  | TRAY           | YES        | 112       | 3-1658044-4 |
| 27.01(1.063) | 40.00(1.575) | 2 | 0.102(.0040) | 58.50(2.303) | 55.20(2.173) | 60.00(2.362)  | YES                  | TRAY           | YES        | 84        | 3-1658044-3 |
| 17.00(.669)  | 20.00(.7874) | 1 | 0.102(.0040) | 38.48(1.515) | 35.20(1.386) | 40.00(1.575)  | YES                  | TRAY           | YES        | 56        | 3-1658044-2 |
| 6.99(.275)   | 0(.000)      | 0 | 0.102(.0040) | 18.49(.728)  | 15.20(.598)  | 20.00(.787)   | YES                  | TRAY           | YES        | 28        | 3-1658044-1 |
| 47.00(1.850) | 80.00(3.150) | 4 | 0.152(.0060) | 98.50(3.748) | 95.20(3.748) | 100.00(3.937) | YES                  | TRAY           | NO         | 200       | 2-1658044-5 |
| 37.02(1.457) | 60.00(2.362) | 3 | 0.152(.0060) | 78.49(3.090) | 75.20(2.961) | 80.00(3.150)  | YES                  | TRAY           | NO         | 160       | 2-1658044-4 |
| 27.01(1.063) | 40.00(1.575) | 2 | 0.102(.0040) | 58.50(2.303) | 55.20(2.173) | 60.00(2.362)  | YES                  | TRAY           | NO         | 120       | 2-1658044-3 |
| 17.00(.669)  | 20.00(.7874) | 1 | 0.102(.0040) | 38.48(1.515) | 35.20(1.386) | 40.00(1.575)  | YES                  | TRAY           | NO         | 80        | 2-1658044-2 |
| 6.99(.275)   | 0(.000)      | 0 | 0.102(.0040) | 18.49(.728)  | 15.20(.598)  | 20.00(.787)   | YES                  | TRAY           | NO         | 40        | 2-1658044-1 |
| -            | 80.00(3.150) | 4 | 0.152(.0060) | 98.50(3.748) | 95.20(3.748) | 100.00(3.937) | NO                   | TRAY           | YES        | 140       | 1-1658044-5 |
| -            | 60.00(2.362) | 3 | 0.152(.0060) | 78.49(3.090) | 75.20(2.961) | 80.00(3.150)  | NO                   | TRAY           | YES        | 112       | 1-1658044-4 |
| -            | 40.00(1.575) | 2 | 0.102(.0040) | 58.50(2.303) | 55.20(2.173) | 60.00(2.362)  | NO                   | TRAY           | YES        | 84        | 1-1658044-3 |
| -            | 20.00(.7874) | 1 | 0.102(.0040) | 38.48(1.515) | 35.20(1.386) | 40.00(1.575)  | NO                   | TRAY           | YES        | 56        | 1-1658044-2 |
| -            | 0(.000)      | 0 | 0.102(.0040) | 18.49(.728)  | 15.20(.598)  | 20.00(.787)   | NO                   | TRAY           | YES        | 28        | 1-1658044-1 |
| -            | 80.00(3.150) | 4 | 0.152(.0060) | 98.50(3.748) | 95.20(3.748) | 100.00(3.937) | NO                   | TRAY           | NO         | 200       | 1658044-5   |
| -            | 60.00(2.362) | 3 | 0.152(.0060) | 78.49(3.090) | 75.20(2.961) | 80.00(3.150)  | NO                   | TRAY           | NO         | 160       | 1658044-4   |
| -            | 40.00(1.575) | 2 | 0.102(.0040) | 58.50(2.303) | 55.20(2.173) | 60.00(2.362)  | NO                   | TRAY           | NO         | 120       | 1658044-3   |
| -            | 20.00(.7874) | 1 | 0.102(.0040) | 38.48(1.515) | 35.20(1.386) | 40.00(1.575)  | NO                   | TRAY           | NO         | 80        | 1658044-2   |
| -            | 0(.000)      | 0 | 0.102(.0040) | 18.49(.728)  | 15.20(.598)  | 20.00(.787)   | NO                   | TRAY           | NO         | 40        | 1658044-1   |
| G            | F            | E | D            | C            | B            | A             | POLYIMIDE FILM PAD ▲ | PACKAGING TYPE | DIFF. PAIR | NO OF POS | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN B. CARBO 30JAN03

CHK D. DIXON 30JAN03

APVD D. DIXON 30JAN03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity Ltd.

NAME  
HEADER ASSEMBLY, 5.0MM [1.97] VERTICAL.  
0.80MM CL.  
MICTOR SB

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A2 00779 C=1658044

SCALE 4:1 SHEET 2 of 2 REV H

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1658044-4](#)