



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		C1	REVISED PER ECO-11-004835	11MAR11	RK	HMR

D



TERMINATED VIEW

C



HOUSING

CONTACT

COVER

B

A

1 MOLDED PARTS: UL RATED 94V-O THERMOPLASTIC, BLACK.



2 CONTACTS: PHOSPHOR BRONZE PER QQ-B-750.

3 CONTACTS: PLATED WITH .000015 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000015 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.

4 POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSITION NUMBER 1 INDICATOR ON 10 AND 14 POSITION PRODUCT.

LOCALIZED GOLD PLATING ON THIS SURFACE

.014 MIN LOCALIZED GOLD PLATE AREA



1.125	2.100	2.380	2.150	43	44	1-1658621-3
1.625	3.100	3.380	3.150	63	64	1-1658621-2
1.525	2.900	3.180	2.950	59	60	1-1658621-1
1.275	2.400	2.680	2.450	49	50	1-1658621-0
1.025	1.900	2.180	1.950	39	40	1658621-9
.875	1.600	1.880	1.650	33	34	1658621-8
.775	1.400	1.680	1.450	29	30	1658621-7
.675	1.200	1.480	1.250	25	26	1658621-6
.625	1.100	1.380	1.150	23	24	1658621-5
.525	.900	1.180	.950	19	20	1658621-4
.425	.700	.980	.750	15	16	1658621-3
.375	.600	.880	.650	13	14	1658621-2
.275	.400	.680	.450	9	10	1658621-1
E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SAMICK 22AUG03	TE TE Connectivity								
DIMENSIONS: INCHES		CHK C. ROHDE 22AUG03									
		APVD M. WALMSLEY 22AUG03	NAME								
		PRODUCT SPEC 108-40000		SIZE A2		CAGE CODE 00779	DRAWING NO C-1658621	RESTRICTED TO -			
MATERIAL SEE NOTES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 5° FINISH SEE NOTES		APPLICATION SPEC 114-40005		WEIGHT -		SCALE 4:1		SHEET 1 of 1	REV C1
		CUSTOMER DRAWING									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1658621-1](#)