



LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER ECO-14-011808	09AUG2014	AP	SB

D

D






1 RCPT CONNECTOR
INSERTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK
SHELLS: STEEL PER ASTM A109, PLATED, .000200 MIN TIN OVER .000100 MIN COPPER UNDERPLATE.




C

C



B

B



FERRULE (MUST BE PURCHASED SEPARATELY)

- 1 RCPT ACCEPTS SIZE 20 SOCKET CONTACTS (CONTACTS MUST BE ORDERED SEPARATELY).
2. ALL PARTS SHIPPED UNASSEMBLED, EACH PART INDIVIDUALLY BULK PACKED.
- 3 SHIELDS: MATERIAL—.020 THICK STEEL, PER ASTM A109, PLATED .000200 MIN TIN OVER .000100 MIN COPPER UNDERPLATE.
- 4 RAISED CAVITY IDENTIFICATION AND AMP TRADEMARK.

1658649-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.REITZEL 31JUL03	TE Connectivity			
DIMENSIONS: INCHES		CHK S.BOLASH 31JUL03				
		APVD M.WALMSLEY 31JUL03	NAME KIT, RCPT, SHIELDING HARDWARE, SIZE 3, 25 ^M POSITION, AMPLIMITE HDP-20			
		PRODUCT SPEC 108-40030				
MATERIAL SEE CALL OUT 3		APPLICATION SPEC 114-40030	SIZE A2	CAGE CODE 00779	DRAWING NO C=1658649	RESTRICTED TO -
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 0° 30'		WEIGHT -	CUSTOMER DRAWING			
FINISH SEE CALL OUT 3		SCALE 4:1	SHEET 1 of 1	REV A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1658649-1](#)