




OBSOLETE	2-166010-8	HOUSING: CLASSIFIED POLYCARBONATE (GREY)	AT CONTACT AREA 0,4 μm Au OVER 1,25 μm Ni. AT POST AREA GOLDFLASH OVER 1,25 μm Ni.
OBSOLETE	2-166010-7		AT CONTACT AREA 2,0 μm Au OVER 1,25 μm Ni. AT POST AREA GOLDFLASH OVER 1,25 μm Ni.
OBSOLETE	2-166010-6		AT CONTACT AREA 3,75 μm Au OVER 1,25 μm Ni. AT POST AREA GOLDFLASH OVER 1,25 μm Ni.
OBSOLETE	2-166010-4		AT CONTACT AREA 0,8 μm Au OVER 1,25 μm Ni. AT POST AREA GOLDFLASH OVER 1,25 μm Ni.
	2-166010-1	CONTACTS: PHOSPHORBRONZE	AT CONTACT AREA 1,25 μm Au OVER 1,25 μm Ni. AT POST AREA GOLDFLASH OVER 1,25 μm Ni.
	ORDER No.	MATERIAL	PLATING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.J.L. AMBAUM 25.08.95	 Tyco Electronics Corporation 's-Hertogenbosch, Nederland				
DIMENSIONS: INCHES		CHK J.GIBBELS	NAME 48 POS. FEMALE RC CONN. ACC. TO DIN 41612, F.48F-CIM WITH MAXI TERMI POINT POSTS				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD					
		PRODUCT SPEC					
		APPLICATION SPEC					
MATERIAL		FINISH	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
-		-	A2	00779	 166010	-	
CUSTOMER DRAWING			SCALE	NTS	SHEET	1 OF 1	REV
							F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-166010-1](#)