



1. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS AT POSITIONS 1 THRU 15
2. POSITIONS 1 THRU 15 WILL ACCEPT SIZE 20 SOCKET CONTACT M39029/63-368 OR AMP PART NO 205090-1
3. UL/CSA DESIGNATION STAMPED IN THIS AREA,OPTIONAL
4. CONTACTS NOT SUPPLIED WITH CONNECTOR



1663036-1

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 12SEP02	TE Connectivity	
DIMENSIONS: INCHES		CHK D.MILLER 12SEP02		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D.MILLER 12SEP02	NAME	
	0 PLC ± -	PRODUCT SPEC	RCPT ASSY,17C2,COAX MIX SIZE 3,AMPLITE WITH FLOAT BUSHINGS	
	1 PLC ± -	APPLICATION SPEC		
MATERIAL SEE CALLOUTS		WEIGHT -	SIZE A1	CAGE CODE 00779
FINISH SEE CALLOUTS		DRAWING NO 1663036		RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1663036-1](#)