



4

3



2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		L	ECR-06-012362	23-05-06	BM	JB
			L1	ECR-08-014461	21-10-08	AEG	WRV



DASHNUMBER	CONNECTOR	POSITION	
		LEFT	RIGHT
-1, -2, -3		c1	c32
-4, -5, -6		c32	c1
-8		a1	a32
1-1		a32	a1



NOTES:

- 1 MATERIAL :
- HOUSING : GLASSFILLED POLYESTER
COLOUR : GRAY
- CONTACTS: PHOSPHORBRONZE
- 2 PLATING CONTACT :
-1 : 2,0 µm Au OVER 1,25 µm Ni AT CONTACT AREA.
REMAINDER TIN PLATING.
-2 : SAME AS -1 ONLY 0,8 µm Au.
-3 : SAME AS -1 ONLY 1,25 µm Au.
-4 : SAME AS -1.
-5 : SAME AS -2.
-6 : SAME AS -3.
-8 : SAME AS -2.
1-1 : SAME AS -2.

WIRE RANGE :
AWG 26-22

INSULATION RANGE :
Ø1,2 MAX.

- 3 COVER 826196-1 CAN BE USED.
- 4 CONNECTOR KIT ASS'Y 166811- AS DELIVERED CONSIST OF A 32 POS. SINGLE ROW CONN. ASS'Y AND A 2x32 POS. DUAL ROW CONN. ASS'Y.
- 5 PRINTED CAVITY-NUMBER ON FRONT AND ON REAR SIDE OF CONNECTOR.
- 6 CONNECTOR PRINTED WITH PARTNUMBER 166811-.

OBSOLETE	SEE NOTE 2	SEE NOTE 1	1-166811-1
			166811-8
			166811-6
			166811-5
			166811-4
			166811-3
			166811-2
OBSOLETE			166811-1
FINISH		MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN J.GIBBELS 03APR96
CHK R.V.LOKVEN
APVD R.SMEETS
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

Tyco Electronics Corporation
's-Hertogenbosch, Nederland

64 POS. BACK PANEL
M.T. CONNECTOR

SIZE A3 CAGE CODE 00779 DRAWING NO C-166811 RESTRICTED TO -

CUSTOMER DRAWING

SCALE NTS SHEET 1 OF 1 REV L1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[166811-5](#)