



注.

- 製品規格番号  
108-500/1による。



A-A 断面



B-B 断面

連鎖状端子型番	バラ状端子型番	材 料	仕 上	適合相手型番	A	B
170030-1	170051-1	黄銅 ±0.4	+	170031 又	11.0	2.0
-2	170051-2	黄銅 ±0.4	錫めっき	は 170089	11.0	2.0
-3	+	黄銅 ±0.4	錫めっき		+	+
-4	170051-3	錫めっき黄銅 ±0.4	+		11.0	2.0
170030-5	+	錫めっき黄銅 ±0.4	+		+	+

OBSOLETE

K2	ECO-17-012711	RS	TD	8/30/17	©1975 BY AMP (Japan), Ltd. ALL RIGHTS RESERVED AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING	参考図面 (CUSTOMER COPY REFERENCE ONLY)
K1	ADDED (P-DWG REV.)	Y.A	gm	1/29/76	材料 (MATERIAL) 表参照	
K	ECN J5-3855	K.Y	gm	1/29/76	仕上 (FINISH) 表参照	
J3	ECN J5-3539	H.S	Y.M	4/2/75	抱合電線断面積 (WIRE RANGE) 0.50 ~ 2.27 mm <sup>2</sup> (AWG #20-14)	
J2	ADDED REDRAWN W/O CHANGES (P-DWG REV.N)	H.S	S.S	7/1/74	被覆外径 (INSULATION DIA) 2.2 ~ 3.4 mm (0.085 ~ 0.135 IN)	
J1		S.K	S.I	7/27/73	分類 (CLASS) 1	型式 (TYPE) オートマチック
LTR	変更 (REVISION RECORD)	DR.	CHK	DATE	一般公差 TOLERANCE EXCEPT AS NOTED ±0.4 ±0.25 ±1.0	尺度 (SCALE) 1
DR.	Y. Koide 7/27/73	DE.			LOC	SIZE
CHK	S. Ishida 7/30/73	APP	Y. Sato 7/30/73		番号 (NO)	REV
					JAC-170080	
					K2	
名称 (NAME) 250シリーズラッチ付タブ						

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[170030-1](#)