






P	LTR	DESCRIPTION	ECN	DATE	OWN	APVD
D1		REVISED PER ECO-11-005030		22MAR11	RK	HMR
D2		REVISED PER ECR-20-009164		6AUG2020	MK	DH




この寸法は嵌合力によって管理する。(BE CONTROLLED BY MATING FORCE) AND NOT TO EXCEED 0.711 MAX

断面 A-A 図 8-1
(SECT) (SCALE)



断面 B-B 図 8-1
(SECT) (SCALE)



断面 C-C 図 8-1
(SECT) (SCALE)

- 注: 1 嵌合するダフの詳細についてはCP-63-048Jの
図面を参照。事
2 製品規格番号 108-5006
△ ストレス除去処理
処理法により外観が変わります。
不活性ガス加熱方式.....無光沢
大気加熱方式.....光沢

NOTES: 1. MATING TAB THK IS 0.762-0.838

2. PRODUCT SPEC: 108-5006

△ STRESS RELIEVING

FINISH IS SUBJECT TO CHANGE BY THE TYPE OF
STRESS RELIEVING PROCESS

INERT GAS FURNACE.....MATTE

ATMOSPHERIC FURNACE FOLLOWED BY ACID PICKLE.....BRIGHT

DIMENSIONS 単位: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED 一般公差 10% ±0.2 30% ±0.25 100% ±0.3 100% ±0.4 100% ±1.0		DWN T. Notario 16 JUL 96 CHK L. Suzuki 18 JUL 96 APP T. Notario 18 JUL 96 PRODUCT SPEC 108-5006 APPLICATION SPEC 114-5084 WEIGHT —		WIRE RANGE 適合電線断面積 0.75~2.27 mm ² (AWG 18-14)		INSULATION DIA 絶縁外径 2.54~4.32 mm	
MATERIAL 108-5006 表参照 (SEE TABLE)				FINISH 仕上 表参照 (SEE TABLE)				CUSTOMER DRAWING	
(250" SERIES FASTON RECEPTACLE) "250" シリーズ ファストン リセプタクル				SIZE A3 CAGE CODE 00779 DRAWING NO. C-170213		SCALE 4-1 SHEET 1 OF 1 REV D2			

型番 (P/N)	材質 (MATERIAL)	仕上 (FINISH)
170213-5	黄銅 (BRASS)	錫めっき (TIN PL)
170213-1	黄銅 (BRASS)	— △
170213-2	黄銅 (BRASS)	錫めっき (TIN PL)
170213-3	黄銅 (BRASS)	錫めっき (TIN PL)
170213-4	黄銅 (BRASS)	— △

OBSOLETE

TE Connectivity

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[170213-5](#)