


P	LTR	DESCRIPTION	DATE	DWN	APVD
A2		LP variants removed. ECR-13-015135	30SEP2013	Abr	Brun
A3		Design 2 and PN 2288140 added. ECR-14-018067	20NOV2014	Bren	Brun
A4		Dimension of ISO-Crimp changed. ECR-17-006253	02MAY2017	HO.	BRUN
A5		WIRE SIZE RANGE 0.22 added. PCN E-17-016682	13NOV2017	MAH.	BRUN



		A5											
	2288140-1	A	0.22-0.35	Sn	A = 2.6 B = 4.2 C = 6.2 D = 14.2 M = 0.8	E = 1.8 G = 1.8	H = 3.9 K = 3.58 N = 3.3 D _{Iso} = 2.6	0.22-0.35	0.9-1.4	967067-2 gelb YELLOW	967056-1 blau / BLUE	963142-2 grau GREY	967056-1 blau / BLUE
1703032-5		A	0.5-0.75	Au	A = 2.8 B = 4.2 C = 6.2 D = 14.2 M = 0.8	E = 2 G = 2.1 D _{Dr} = 1	H = 4.4 K = 4 L = 1.5 N = 3.5 D _{Iso} = 2.9	0.5-0.75	1.4-1.9	967067-1 gruen GREEN		963142-1 schwarz BLACK	
1703032-1		A		Sn									
Bestell-Nr. ORDER NO. DESIGN 1	Bestell-Nr. ORDER NO. DESIGN 2	Rev	DGB Wire Size Range mm ²	Oberflaeche SURFACE	Laenge LENGTH mm	Drahtcrimp WIRE CRIMP mm	Iso-crimp INSU-CRIMP mm	DGB Wire Size Range mm ²	Isolations Ø INSULATION DIA. mm	fuer Kammer Ø3.45 FOR CAVITY DIA. 3.45 mm	Blindstopfen RUBBER PLUG	fuer Kammer Ø4 FOR CAVITY DIA. 4 mm	Blindstopfen RUBBER PLUG
zugehoerige Einzeldichtung / SUITABLE SINGLE WIRE SEAL													

1471-9 (3/11)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

1 PLC ±0.2

2 PLC ±0.2

3 PLC ±0.2

4 PLC ANGLES ±°

MATERIAL -

FINISH -

DWN Abraham.G. 01JUN2004

CHK Kampmann.H. 02JUN2004

APVD Bleicher.M. 27SEP2004

PRODUCT SPEC 108-18030

APPLICATION SPEC 114-18025

WEIGHT 0.13 g

Customer Drawing

NAME MQS SOCKET CONTACT CLEANBODY SWS Tabellenzzeichnung Buchsenkontakt

SIZE A2

CAGE CODE 00779

DRAWING NO C=1703040

RESTRICTED TO -

SCALE 10:1

SHEET 1 of 1

REV A5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1703032-1](#)