




P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	REVISED PER ECO-19-005751	26SEP2019	RS	SG



- 1. THIS CONTACT IS USED ON EITHER PLUG AND CAP HOUSING
- 2 0.00076mm MIN THICK GOLD-PLATED IN THE CONTACT SECTION TO 3.2mm FROM TIP END, OVER NICKEL UNDERPLATE ALL OVER
- 3. WIRE RANGE: 22-18 AWG
INSULATION DIA: 1.5-2.4mm
- 4. APPLICABLE INSULATION DIA MAX FOR TWO WIRE CRIMP IS 3.4mm MAX

170361, 170362, 170365, 170366	TIN/PHOS BRONZ	170364-4	170360-4
	GOLD/BRASS 	170364-3	170360-3
	TIN/BRASS	170364-1	170360-1
MATING P/N	FINISH/MATERIAL	LOOSE PIECE P/N	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±0.3
1 PLC	±0.3
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL
SEE TABLE

FINISH
SEE TABLE

DWN
R. SMITH
26SEP2019

CHK
S. WRIGHT
26SEP2019

APVD
S. WRIGHT
26SEP2019

PRODUCT SPEC
108-5138

APPLICATION SPEC
114-5050

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
MINI UNIVERSAL MATE-N-LOK
PIN CONTACT
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-170360

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
L

1470-19 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[170360-1](#)