


LOC	DIST	REVISIONS 変更				DATE	DWN	APVD
J		P	LTR	DESCRIPTION				
			C2	REVISED PER ECO-11-005030		11MAR11	RK	HMR



- 1 使用ハウジング
172213-*: パネル取付型
172211-*: 宙吊り型
- 2 適用規格
製品規格: 108-5118
取付適用規格: 114-5035
- 3 バラ状端子用手動工具 724685-1
- ④ めっき仕様: ニッケル下地、
接触ピン部のみ金めっき 0.38μ以上

- 1 APPLICABLE HOUSINGS
172213-*: PANEL MOUNT TYPE
172211-*: FREE HANGING TYPE
- 2 SPECIFICATIONS
PRODUCT SPEC.: 108-5118
APPLICATION SPEC.: 114-5035
- 3 HAND TOOL: 724685-1
- ④ FINISH: 0.00038 MIN GOLD PLT AT PIN AREA
OVER Ni PLT

GENERAL TOLERANCE
一般公差

10 ≥: ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

↑ -3	磷青銅0.2厚 ④	PHOS-BZ 0.2t ④	↑ -3
-2	錫めっき済磷青銅0.2厚	PRE-TIN PLT PHOS-BZ 0.2t	-2
170429-1	錫めっき済黄銅0.2厚	PRE-TIN PLT BRASS 0.2THK	170376-1
バラ状端子 LOOSE PIECE	材質・仕上	MATERIAL & FINISH	型番 PART NO

WIRE RANGE 包合電線断面積	(AWG#20-#26) 0.14~0.52 mm ²	INSULATION DIA 被覆外径	1.1~1.9 mm
-----------------------	---	------------------------	------------

DIMENSIONS: 単位: 耗 mm		DWN TSUKAKOSHI 26MAY1980	MATERIAL 材料 表参照 SEE TABLE		FINISH 仕上 表参照 SEE TABLE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		CHK N.ONOUE 30MAY1980				
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD - 30MAY1980				
PRODUCT SPEC 製品規格		NAME 名称 EI シリーズ コネクタ ピンコンタクト (AWG#20-#26) PIN CONTACT, AWG 20-26 EI SERIES CONNECTOR				
APPLICATION SPEC 取付適用規格		SIZE A4				
WEIGHT -		CAGE CODE 00779				
CUSTOMER DRAWING		DRAWING NO 番号 170376				
SCALE 尺度 4:1		RESTRICTED TO -				
SHEET 1 OF 1		REV C2				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[170376-2](#)