




(SIMULATIVE NO. 200532-2)  
類似 NO. 200532-2


|        |                           |     |      |            |
|--------|---------------------------|-----|------|------------|
| H      | REVISED PER ECO-20-007658 | KR  | MZ   | 12JUN 2020 |
| G      | REVISD                    | T.N | N.Y  | 09SEP 2011 |
| F      | 改訂 (EJ00-0246-93)         | Y.T | S.H  | 1/8/20     |
| E      | REVISED (0886910)         |     |      | 1/8/20     |
| E      | ADDED -3 (P-DWG REVIE)    |     |      | 1/8/20     |
| D      | OBSOLETE -1 (P-DWG)       |     |      | 1/8/20     |
| C      | ADDED -2 (P-DWG REV. G.I) |     |      | 1/8/20     |
| C      | REVISED                   |     |      | 1/8/20     |
| B      | REVISED (P-DWG)           |     |      | 1/8/20     |
| A      | REVISED (P-DWG)           |     |      | 1/8/20     |
| O      | RELEASED (REV. A.)        |     |      | 1/8/20     |
| L.T.R. | 寫真 (REVISION RECORD)      | DR. | CHK. | DATE       |

NO. (NUMBER)  
C-171050

| 組立部品     | (REQUIRED PER ASSEMBLY) |
|----------|-------------------------|
| 7-474050 |                         |
| 171050   |                         |
| 171050   |                         |
| 171050   |                         |

[illegible]

(NOTE)  
 注記: 1. 最大電線束線径:  $\phi 18$ . (1. MAX. CABLES DIA.:  $\phi 18$  )  
 2. 最小電線束線径:  $\phi 12$ . ( MIN. CABLES DIA.:  $\phi 12$  )  
 △ ウィスカー対策・RoSH対応品  
 (WHISKER COUNTERMEASURE & RoSH COMPLIANCE)



© COPYRIGHT 2012 BY Tyco Electronics Japan G.K.

参考図面  
(CUSTOMER COPY)  
(REFERENCE ONLY)

|                                 |                                                                                                                                        |                                                                                                       |                                  |
|---------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|----------------------------------|
| 材料 (MATERIAL) (SEE DWG.)<br>上参照 | 線全規格詳細図 (WIRE RANGE)<br><br>mm <sup>2</sup> (AWG) |  TE Connectivity |                                  |
| 仕上 (FINISH) (SEE DWG.)<br>上参照   | 被覆外径 (INSULATION DIA.)<br><br>mm (IN)             | 分類 (CLASS)<br>— H —                                                                                   | 型式 (TYPE)<br>— H —               |
| DR.                             | 一般公差<br>[TOLERANCE EXCEPT AS NOTED] ±0.4<br>±1.0                                                                                       | 尺取 (SCALE)<br>   | LOC SIZE 番目 (NO)<br>J B C-171050 |
| CHK<br>22/1/2014 30/4/1         | 名称 (NAME)<br>50極 180°<br>(50 PIN 180°)                                                                                                 | ショート シールド<br>(SHORT SEALED)                                                                           |                                  |
| DE.                             |                                                                                                                                        |                                                                                                       | REV.<br>H                        |
| APPR<br>26/1/11                 |                                                                                                                                        |                                                                                                       |                                  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[171050-2](#)