





LOC J	DIST —	REVISIONS 変更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			R1	ALTERNATE RESIN UPDATE FOR 1—171370—2	12MAR2020	SE	PKS



断面 "A" - "A"
SECT



矢視 "M" 1-171370-2
VIEW



矢視 "M" 1-171370-1
VIEW

注記

- 一般公差 : ±0.2
- 適用ピン リセプタクル型番 : □ -170063-□ , □ -353937-□ , □ -1123655-□
- 適用規格番号 : 108-5143 (型番1-171370-1)

- 裏面上I.Dマーク : 型番1-171370-1のみ M 表示 文字の向きは任意とする。
- ミューラスRタイプ: UL94V-0 , CTI 600V
- フェノール ノンアンモニア: UL94V-0 , CTI 175 ~ 249V以上
- 裏面上I.Dマーク : 型番1-171370-2のみ L 表示 文字の向きは任意とする。

NOTES:

- GENERAL TOLERANCE ±0.2
- APPLICABLE CONTACT PART No.: □ -170063-□ , □ -353937-□ , □ -1123655-□
- PRODUCT SPEC No.: 108-5143 (1-171370-1)

- I.D MARK ON REAR SIDE : INDICATION M
AT PART No.1-171370-1 ONLY.
DIRECTION OF CHARACTERS IS FREE.
- MEWLUS "R" TYPE : UL94V-0 , CTI 600V MIN
- PHENOLIC NONAMMONIA UL94V-0 , CTI 175 ~ 249V
- I.D MARK ON REAR SIDE : INDICATION L
AT PART No.1-171370-2 ONLY.
DIRECTION OF CHARACTERS IS FREE.

1-171370-2	フェノール (PHENOLIC)	黒 (BLACK)
1-171370-1	ミューラス Rタイプ (MEWLUS "R" TYPE)	黒 (BLACK)
型番 (PART No.)	材料 (MATERIAL)	色 (COLOR)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.SUZUKI 21MAY2002	TE Connectivity			
DIMENSIONS: 単位: 耗 mm		CHK M.SHINDO 21MAY2002				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD M.SHINDO 21MAY2002	NAME 名称 2.3 DIA CLUSTER BLOCK Φ2.3 クラスタブロック			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 製品規格 SEE NOTES 3.				
MATERIAL 材料 SEE TABLE		APPLICATION SPEC 取付適用規格	SIZE A3 CAGE CODE 00779 DRAWING NO 番号 171370 RESTRICTED TO —			
FINISH 仕上		WEIGHT				
CUSTOMER DRAWING				SCALE 尺度 4:1	SHEET 1 of 3	REV R1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


MAY ,21 .

© COPYRIGHT 02

By -


ALL RIGHTS RESERVED.

LOC J	DIST	REVISIONS 變更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—




- 注記
- 一般公差 : ± 0.2
 - 適用ピン リセプタクル型番 : □ -170063-□ , □ -353937-□ , □ -1123655-□
 - 適用規格番号: 108-5205(型番171370-3)
108-61239(型番171370-4)
108-5541(型番171370-5)
- △4 PARTS COMPLY WITH GLOW WIRE 750 PER IEC 60335-1.
△5 MUST BE APPLIED ON THE OUTSIDE OF COMPRESSOR.

- NOTES;
- GENERAL TOLERANCE ± 0.2
 - APPLICABLE CONTACT PART No.:
□ -170063-□ , □ -353937-□ , □ -1123655-□
 - PRODUCT SPEC No.: 108-5205(FOR PART No.171370-3)
108-61239(FOR PART No.171370-4)
108-5541(FOR PART No.171370-5)
- △4 GLOW WIRE 750(IEC 60335-1), CTI 600V(HALOGEN FREE)
△5 MUST BE APPLIED ON THE OUTSIDE OF COMPRESSOR.






断面 "A" - "A"
SECT






断面 "B" - "B"
SECT

171370-5	PBT ガラス強化 PBT GLASS FILLED(UL94V-0)	灰色 (GRAY)
171370-4	PBT ガラス強化 PBT GLASS FILLED(UL94V-0)	黒 (BLACK)
171370-3	PBT ガラス強化 PBT GLASS FILLED(UL94HB)	自然色 (NATURAL)
型番 (PART No.)	材料 (MATERIAL)	色 (COLOR)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity			
DIMENSIONS: 単位: 耗 mm		CHK				
		APVD	NAME 名称			
		PRODUCT SPEC 製品規格	2.3 DIA CLUSTER BLOCK			
MATERIAL 材料		APPLICATION SPEC 取付適用規格	Φ2.3 クラスタブロック			
		WEIGHT	SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
SEE TABLE		CUSTOMER DRAWING	A3	00779	C-171370	-
			SCALE 尺度	4:1	SHEET 2 of 3	REV R1



LOC J	DIST	REVISIONS 变更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



- 注記
- 一般公差 : ± 0.2
 - 適用ピン リセプタクル型番 : □ -170063-□ , □ -353937-□ , □ -1123655-□
 - 適用規格番号: 108-140004 (型番171370-7)
 - PRELIMINARY-NOT FOR PRODUCTION
 - PARTS COMPLY WITH GLOW WIRE REQUIREMENTS DETAILED IN IEC 60335-1

- NOTES;
- GENERAL TOLERANCE ± 0.2
 - APPLICABLE CONTACT PART No. : □ -170063-□ , □ -353937-□ , □ -1123655-□
 - PRODUCT SPEC No.: 108-140004 (FOR PART No.171370-7)
 - PRELIMINARY-NOT FOR PRODUCTION
 - PARTS COMPLY WITH GLOW WIRE REQUIREMENTS DETAILED IN IEC 60335-1
 - PRELIMINARY PART

△6	171370-8	PPS (UL94V-0)	(NATURAL)
△5	171370-6	PA 6 GLASS FILLED	自然色 (NATURAL)
	171370-7	液晶ポリマー (UL94V-0) LCP (UL94V-0)	自然色 (NATURAL)
	型番 (PART No.)	材料 (MATERIAL)	色 (COLOR)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity			
DIMENSIONS: 単位: 耗 mm		CHK				
		APVD	NAME 名称 2.3 DIA CLUSTER BLOCK Φ2.3 クラスターブロック			
		PRODUCT SPEC 製品規格 SEE NOTE 3				
MATERIAL 材料 SEE TABLE		APPLICATION SPEC 取付適用規格	SIZE A3			
		WEIGHT	CAGE CODE 00779			
		CUSTOMER DRAWING	DRAWING NO 番号 C=171370			
			RESTRICTED TO —			
			SCALE 尺度 4:1		SHEET 3 of 3	REV R1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[171370-5](#)