











REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
01		REVISED ECR-05-012980	18OCT05	TS	KB
02		REVISED ECR-09-010587	14MAY09	KF	HY
A		REVISED ECR-09-023330	26NOV09	TS	KB
A1		ECR-20-001927	11FEB2020	VI	MT



1. POSITION TOLERANCE $\oplus \begin{matrix} \text{Ø} 0.1 \text{ S} \\ \text{G G-H} \end{matrix}$ を適用すること

2. POSITION TOLERANCE $\oplus \begin{matrix} \text{Ø} 0.1 \text{ S} \\ \text{G G-S} \end{matrix}$ を適用すること

3. MEASURED AT 6mm FROM -Z- 面より6mmの位置で測定

4. 最大寸法で管理
5. 適合相手コネクタ品番: TABLE-1 参照
6. 端子構成: TABLE-2 参照
7. 本製品の取扱は取扱説明書 No. 411-78145 に従うこと
8. 適用基板の厚さは 1.6mm
9. 実装時の半田ペーストの厚さは 0.15mm 以上

1. POSITION TOLERANCE $\oplus \begin{matrix} \text{Ø} 0.1 \text{ S} \\ \text{G G-H} \end{matrix}$

2. POSITION TOLERANCE $\oplus \begin{matrix} \text{Ø} 0.1 \text{ S} \\ \text{G G-S} \end{matrix}$

3. MEASURED AT 6mm FROM -Z-

4. MUST BE CONTROLLED AT MAXIMUM DIMENSION

5. MATING CONNECTOR PART NO.: SEE TABLE-1

6. DETAIL OF TERMINALS: SEE TABLE-2

7. HANDLING OF THIS PART SHOULD FOLLOW INSTRUCTION SHEET NO. 411-78145

8. APPLICABLE PRINTED CIRCUIT BOARD'S THICKNESS 1.6mm

9. WHEN MOUNTING, THICKNESS OF SOLDER PASTE; 0.15mm MIN.

TABLE-2

POS. 極数	FINISH	TYPE
16	TIN	0.64

TABLE-1

POS. 極数	TYPE	P/N
16	0.64 CRIMP	1318386
16	0.64111 CRIMP	1717109
16	0.64 IDC	1318692

OUTER 分装	PAPER BOX タンボール箱	PAPER BOX タンボール箱	PLASTIC BOX 通い箱	PACKING STYLE 梱包形態			
INNER 内装	TRAY トレイ	PLASTIC TUBE プラスチックチューブ	PLASTIC TUBE プラスチックチューブ				
	SAME AS 1717396-1	SAME AS 1717396-1	2	SOLDER PEG	POST-TIN	4	
			8	0.64 TAB CONTACT (L)	POST-TIN	3	
			8	0.64 TAB CONTACT (S)	POST-TIN	2	
			1	16P CAP HOUSING	BLACK	1	
	1717396-3	1717396-2	1717396-1	NAME	FINISH/COLOR	NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y. KAWAHARA 06JAN2005	06JAN2005		 TE Connectivity						
DIMENSIONS: mm		CHK H. YAMAGAMI 06JAN2005	06JAN2005								
TOLERANCES UNLESS OTHERWISE SPECIFIED: mm		APVD S. ISHOTA 06JAN2005	06JAN2005		NAME 0.64 SMD CONNECTOR 16 POSITION CAP ASSEMBLY V-TYPE						
0-PLC 1-PLC 2-PLC 3-PLC 4-PLC		PRODUCT SPEC 108-78295		SIZE 6.7 g		CAGE CODE A		DRAWING NO C-1717396		RESTRICTED TO A	
ANGLES °		APPLICATION SPEC 114-5250, -5329, -5276									
FINISH SEE TABLE		WEIGHT 6.7 g		CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1		REV A	
MATERIAL HOUSING : PPS GF40 CONTACT : BRASS											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1717396-2](#)