





PRINT DIST

単位: mm DIMENSIONS IN MM. DO NOT SCALE PRINT

METRIC



NUMBER
C-172128



1. 嵌合する相手ハウジングは型番172127
2. 使用端子は型番170032, 170258, 170384
- △ 本品はUL難燃グレード94V-0に適合する材料により作られている
4. 製品規格: 108-5147
5. 認定試験報告書: 501-5050

1. THE MATING CAP HOUSING, P/N 172127
2. APPLIED CONTACT, P/N 170032, 170258, 170384
- △ THIS ITEM IS MADE FROM MATERIALS APPLICABLE TO UL FLAME CLASS 94V-0
4. PRODUCT SPECIFICATION: 108-5147
5. QUALIFICATION TEST REPORT: 501-5050

△ 6. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE
△ 6

淡灰 (LIGHT GRAY)	6-172128-6
自然色 (NATURAL)	△ 1-172128-1
赤 (RED)	172128-9
橙 (ORANGE)	172128-8
黄 (YELLOW)	172128-7
灰 (GRAY)	172128-6
青 (BLUE)	172128-5
緑 (GREEN)	172128-4
茶 (BROWN)	172128-3
黒 (BLACK)	172128-2
自然色 (NATURAL)	172128-1
色 (COLOR)	型番 (P/N)

TE TE Connectivity

絶縁電線断面積 (WIRE RANGE)		被覆外径 (INSULATION DIA.)		名称 (NAME)	
mm ² (AWG)		mm ²		250 シリーズ ハウジングランスコネクタ	
材料 (MATERIAL)		仕上 (FINISH)		1極 プラグ ハウジング	
66 ナイロン (66 NYLON)		仕上 (FINISH)		250 SERIES HOUSING LANCE CONNECTOR 1POE PLUG HOUSING	
E4 REVISED PER ECO-11-005030		RK	HMR	25APR11	一般公差 (GENERAL TOLERANCE)
LTR 変更 (REVISION RECORD)		DR	CHK	DATE	10mm以下: ±0.2
CHK. K. B. 4/6'93		DE. T. Yamagami 4/6'93		10mm超え 30mm以下: ±0.25	
APP. B. Ogama 4/6'93		APP. B. Ogama 4/6'93		30mm超え 100mm以下: ±0.3	
				角 度: ±3°	
				尺 度 (SCALE)	
				2-1	
				REV. E4	
				SHEET 1 OF 1	

(CUSTOMER DRAWING) 参 考 図 面

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[172128-2](#)