








寸法公差は±0.20
(TOLERANCE : ±0.2)
パネル取付穴
(DIMENSION OF PANEL)

NOTES:

1. APPLIED CONTACT P/N : 170359 . 170360 . 170361 . 170362
2. MATING CONN ; PLUG HOUSING P/N 172337
3. PANEL THICKNESS : 0.8 ~ 2.0 mm
4. PRESS DIRECTION OF PANEL MUST BE SAME AS HOUSING INSERTED DIRECTION.
5. INSTRUCTION SHEET : IS - 105J
6. PRODUCT SPEC : 108 - 5151
7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

注:

1. 使用端子型番は、170359, 170360, 170361, 170362
2. 嵌合相手ハウジング型番は、172337
3. 適用パネル厚 0.8 ~ 2.0 mm
4. 取付穴打抜方向とハウジングの挿入方向は同じとする。
5. 取扱説明書 : IS-105J
6. 適用製品仕様書 : 108-5151

OBSOLETE

黄 (YELLOW)	1- 172329 - 4
黒 (BLACK)	1- - 9
青 (BLUE)	1- - 6
緑 (GREEN)	1- - 5
赤 (RED)	1- - 2
自然色 (NATURAL)	172329 - 1
色 (COLOR)	型番 (P/N)

材料 (MATERIAL) 6/6 ナイロン (UL94V-2) (NYLON 6/6 UL94V-2)	一般公差 TOLERANCE ± 0.3 EXCEPT ± 1° AS NOTED	TE Connectivity	
仕上 (FINISH) 色: 表参照 HOUSING : SEE TABLE COLOR	DR. R. Yano 1/21/81 CHK. J. Taniguchi 1/21/81 DE. APP.	名称 (NAME) MINI-UNIVERSAL MATE-N-LOK CONN. CAP HOUSING 3Pos (UL94V-2) 3極 ミニユニバーサルメイトンロックコネクタ キャップハウジング (UL94V-2) SIZE LOC 番号 (NO.) B J C-172329	
尺度 (SCALE) 2 : 1		REV. A3	SHEET

(CUSTOMER DRAWING) 参考図面

A3	REVISED PER ECO-11-005030	RK	HMR	23MAR11
LTR.	変更 (REVISION RECORD)	DR.	CHK.	DATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-172329-2](#)