






PRINT DIST

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

METRIC

NUMBER C-172777

3rd ANGLE PROJECTION



- 注:
1. 適合相手リセプタクル型番 172773, 172774
  2. 製品規格 No. 108-5166
  3. 取付適用規格 114-5072
  4. 相手ハウジング型番 172518 他
- △ 逆巻きリール

- NOTES:
1. MATE TAB P/N 172773, 172774
  2. PRODUCT SPEC. No. 108-5166
  3. APPLICATION SPEC. No. 114-5072
  4. PLUG HSG P/N 172518 ETC.
- △ REVERSE REEL

172778-1	錫メッキ済 (PRE-TIN)	黄銅 (BRASS)	△1-172777-1	4
172778-4	錫メッキ済 (PRE-TIN)	黄銅 (PHOS BR)	172777-4	3
172778-2	金メッキ (SELECTIVE GOLD)	黄銅 (BRASS)	172777-2	2
172778-1	錫メッキ済 (PRE-TIN)	黄銅 (BRASS)	172777-1	1
タブ端子型番 (LP NO.)	仕上 (FINISH)	材料 (MATERIAL)	型番 (P/N)	項目 (ID)

				(P.N)		(D)			
				© 19 BY AMP (Japan) LTD. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND OR PATENTS PENDING		AMP		AMP (JAPAN), LTD. Tokyo, Japan	
				WIRE RANGE 0.5~2.27 mm <sup>2</sup> (AWG#20~#14)		INSULATION DIA 2.2~3.4 mmφ		NAME タブコンタクト マルチインターコネクタ (MIC) マーク II TAB MIC MK II	
				MATERIAL 表参照 SEE TABLE		FINISH 表参照 SEE TABLE		GENERAL TOLERANCE 0<≦ 10 : ±0.2 10<≦ 30 : ±0.25 30<≦ 100 : ±0.3 ANGLES : ±3°	
J-10629				DR. H. B. B. 1/19/84		DE. H. B. B. 1/19/84		SIZE LOC NUMBER B J C-172777	
C REDRAWN W/CHANGE				CHK. B. B. 1/19/84		APP. H. B. B. 1/19/84		SCALE REV. SHEET 5-1 C 1 OF 1	
LTR REVISION RECORD				DR		CHK DATE			

CUSTOMER DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[172777-1](#)