





OBSOLETE	3.91	BLACK (426C)	15u"	4-1734309-7
		BEIGE (726C)	15u"	2-1734309-8
		BLACK (426C)	15u"	2-1734309-7
OBSOLETE		BEIGE (726C)	30u"	2-1734309-6
		BLACK (426C)	30u"	2-1734309-5
OBSOLETE	2.84	BEIGE (726C)	5u"	2-1734309-4
OBSOLETE		BLACK (426C)	5u"	2-1734309-3
OBSOLETE		BEIGE (726C)	C/F	2-1734309-2
OBSOLETE		BLACK (426C)	C/F	2-1734309-1
△ OBSOLETE		BEIGE (726C)	15u"	1734309-8
△ OBSOLETE		BLACK (426C)	15u"	1734309-7
△ OBSOLETE		BEIGE (726C)	30u"	1734309-6
		BLACK (426C)	30u"	1734309-5
△ OBSOLETE	2.2	BEIGE (726C)	5u"	1734309-4
		BLACK (426C)	5u"	1734309-3
OBSOLETE		BEIGE (726C)	C/F	1734309-2
OBSOLETE		BLACK (426C)	C/F	1734309-1
	DIM A	HOUSHING COLOR	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HSING 06FEB2009	TE Connectivity	
		CHK S. CHIEN 06FEB2009		
		APVD W. KODAMA 06FEB2009	NAME	
DIMENSIONS: MM		PRODUCT SPEC 108-57519	TRIPLE STACKED USB, A TYPE, RECEPTACLE, R/A, DIP CONN.	
		APPLICATION SPEC		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT 9.2 GRAMS	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C=1734309	RESTRICTED TO
MATERIAL SEE NOTE		FINISH SEE NOTE	SHEET 1 OF 3	REV D3






D

C


B

A


100PCS/TRAY



10 LAYERS



CARTON



13.0	12.0	100	10	1000
G/W (KG)	N/W (KG)	PCS/TRAY	TRAY/CARTON	PCS/CARTON

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:MM

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZECAGE CODEDRAWING NORESTRICTED TO

TE Connectivity

TRIPLE STACKED USB, A TYPE, RECEPTACLE, R/A, DIP CONN.

A300779C=1734309

SCALE

SHEET 3 OF 3

REV D3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1734309-5](#)