




DIMENSIONS: mm ((+))SEE NOTE







RIGHT ANGLE PLUG ASS WITH RIGHT ANGLE RECEP

NOTE:

- 1. MATERIAL:
- HOUSING: LCP, UL 94V-0, COLOR: BLACK. CONTACT: PHOSPHOR BRONZE, THICKNESS=0.30mm.
- RETENTION LEGS: BRASS, THICKNESS=0.50mm.
- 2. FINISH:
- CONTACT: GOLD FLASH OVER


0.762um [30u"] MIN. PALLADIUM-NICKEL PLATED ON (3.8um [150u"] MIN. MATTE TIN PLATED ON SOLDER TAI 1.27um [50u"] MIN. NICKEL UNDERPLATED ALL OVER. RETENTION LEGS: 3.8um [150u"] MIN. TIN-CU PLATED OVER 1.27um [50u"] MIN. NICKEL PLATED.


- 3. AIWAYS RoHS/ELV COMPLIANT
- 4. WAVE SOLDER CAPABLE TO 265°C PER TE SPEC 109-202, CONDI


A CO	NTROLL	ED DOCUMENT.	dwn O. HU	240CT2006		
			О. ПО СНК S НОЦ	240CT2006		
		ERANCES UNLESS RWISE SPECIFIED:	apvd W.J. KE	240CT2006	NAME	
	0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES	± 0.38 ± 0.25 ± 0.13 ± 0.05 $\pm -$ $\pm 3^{\circ}$	PRODUCT SPEC 108-57 APPLICATION SPEC	7876	SIZE	(
	FINISH		WEIGHT		AЗ	C
		SEE NOTE	CUSTOMER	DRAWING		

9, IMPROVE 2041003–1 HSG STRUCTURE AND 11JAN'11 E.L. W.K.	
	D
	С
SSEMBLY MATED EPTACLE ASSEMBLY	
N CONTACT AREA,	B
AILS, R.	
IDITION B.	
REVERSED 1734375–1 INTERFACE PART NUMBER	
TE Connectivity	
CHAMP 1.27, SERIES I, PLUG, ASS'Y, R/A, EXTENDED HEIGHT	٨
CAGE CODE DRAWING NO RESTRICTED TO	
00779 C-1734375	


DATE	DWN	APVD
) 11JAN'11	E.L.	W.K.
		date dwn ^d 11jan'11 E.L.








LOC DIST REVISIONS	2						1				
		LOC	DIST				REVISIONS				
DW F LTR DESCRIPTION DATE DWN		DW		Ρ	LTR		DESCRIPTION		DATE	DWN	APVD
SEE SHEET 1.						SEE SHEET 1.					



7.80 2.40 1 2.40 1 1.905 1 1.	
	В
NORMAL 1-1734375-1 INTERFACE PART NUMBER S A CONTROLLED DOCUMENT. TOLERANCES UNLESS OTHERWISE SPECIFIED: PRODUCT SPEC PRODUCT SPEC PROD	A


D



THIS DRAWING IS A DIMENSIONS: mm MATERIAL

<u> </u>	- DITATRITNA	9MA

	2				
LOC	DIST	Ρ	LTR		
				SEE SHEET 1.	



		2.46	1.46		
		G.W(KGS)	N.W(KG	S) PA(CK,
5 A CONTROLLED DOCUMENT.	DWN				
	CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD			NAME	
$ \begin{array}{c} 0 \ PLC & \pm - \\ 1 \ PLC & \pm - \\ 2 \ PLC & \pm - \end{array} $	PRODUCT SP	EC			
$\begin{array}{c} - \\ - \\ - \\ - \\ - \\ - \\ - \\ - \\ - \\ - $	APPLICATION	SPEC		SIZE	C
FINISH	WEIGHT			AJ	
	CUSTOM	IER DRAW	ING		

				С
				B
128	8	16	1 - 1734375 - 1	
(aging quantity/box	TRAY/BOX	PCS/TRAY	PART NUMBER	
E TE	TE Cor	nectivity		
CHAMP 1.2	7, SERIES	SI, PLUG,		
ASS'Y, R/A,	EXTENDE	ED HEIGHT		A
CAGE CODE DRAWING NO	1 7 7 5		RESTRICTED TO	
00779 C-1734		SHEET –	REV C	
		<u> </u>	of 3	

D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity: <u>1734375-1</u>