




4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

MAR , 2006.

© COPYRIGHT 2009 By -

ALL RIGHTS RESERVED.

LOC  
IRDIST  
—

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
| — | —   | SEE SHEET 1 | —    | —   | —    |

CONNECTOR

BOX

314mm(L)\*128mm(W)\*11mm(H)

OUTER CARTON

340mm(L)\*295mm(W)\*320mm(H)


CORRUGATE PAPER

INNER CARTON

320mm(L)\*138mm(W)\*144mm(H)

|          |  |       |       |      |    |   |   |   |   |
|----------|--|-------|-------|------|----|---|---|---|---|
| OBSOLETE |  | 5040  | 1260  | 105  | 40 | 9 | — | — | 9 |
| OBSOLETE |  | 4320  | 1080  | 90   | 50 | 9 | — | — | 8 |
| OBSOLETE |  | 4320  | 1080  | 90   | 48 | 9 | — | — | 7 |
| OBSOLETE |  | 4320  | 1080  | 90   | 46 | 9 | — | — | 6 |
| OBSOLETE |  | 4320  | 1080  | 90   | 44 | 9 | — | — | 5 |
| OBSOLETE |  | 5040  | 1260  | 105  | 42 | 9 | — | — | 4 |
| OBSOLETE |  | 5040  | 1260  | 105  | 40 | 9 | — | — | 3 |
| OBSOLETE |  | 5040  | 1260  | 105  | 38 | 9 | — | — | 2 |
| OBSOLETE |  | 5760  | 1440  | 120  | 36 | 9 | — | — | 1 |
| OBSOLETE |  | 5760  | 1440  | 120  | 34 | 9 | — | — | 0 |
| OBSOLETE |  | 6480  | 1620  | 135  | 32 | 8 | — | — | 9 |
| OBSOLETE |  | 7200  | 1800  | 150  | 30 | 8 | — | — | 8 |
| OBSOLETE |  | 7200  | 1800  | 150  | 28 | 8 | — | — | 7 |
| OBSOLETE |  | 7920  | 1980  | 165  | 26 | 8 | — | — | 6 |
| OBSOLETE |  | 8640  | 2160  | 180  | 24 | 8 | — | — | 5 |
| OBSOLETE |  | 9360  | 2340  | 195  | 22 | 8 | — | — | 4 |
| OBSOLETE |  | 10080 | 2520  | 210  | 20 | 8 | — | — | 3 |
| OBSOLETE |  | 11520 | 2880  | 240  | 18 | 8 | — | — | 2 |
| OBSOLETE |  | 12960 | 3240  | 270  | 16 | 8 | — | — | 1 |
| OBSOLETE |  | 15120 | 3780  | 315  | 14 | 8 | — | — | 0 |
| OBSOLETE |  | 17280 | 4320  | 360  | 12 | 7 | — | — | 9 |
| OBSOLETE |  | 20880 | 5220  | 435  | 10 | 7 | — | — | 8 |
| OBSOLETE |  | 26640 | 6660  | 555  | 8  | 7 | — | — | 7 |
| OBSOLETE |  | 35280 | 8820  | 735  | 6  | 7 | — | — | 6 |
| OBSOLETE |  | 51840 | 12960 | 1080 | 4  | 7 | — | — | 5 |
| OBSOLETE |  | 4320  | 1080  | 90   | 50 | 7 | — | — | 4 |
| OBSOLETE |  | 4320  | 1080  | 90   | 48 | 7 | — | — | 3 |
| OBSOLETE |  | 4320  | 1080  | 90   | 46 | 7 | — | — | 2 |
| OBSOLETE |  | 4320  | 1080  | 90   | 44 | 7 | — | — | 1 |
| OBSOLETE |  | 5040  | 1260  | 105  | 42 | 7 | — | — | 0 |
| OBSOLETE |  | 5040  | 1260  | 105  | 40 | 6 | — | — | 9 |
| OBSOLETE |  | 5040  | 1260  | 105  | 38 | 6 | — | — | 8 |
| OBSOLETE |  | 5760  | 1440  | 120  | 36 | 6 | — | — | 7 |
| OBSOLETE |  | 5760  | 1440  | 120  | 34 | 6 | — | — | 6 |
| OBSOLETE |  | 6480  | 1620  | 135  | 32 | 6 | — | — | 5 |
| OBSOLETE |  | 7200  | 1800  | 150  | 30 | 6 | — | — | 4 |
| OBSOLETE |  | 7200  | 1800  | 150  | 28 | 6 | — | — | 3 |
| OBSOLETE |  | 7920  | 1980  | 165  | 26 | 6 | — | — | 2 |
| OBSOLETE |  | 8640  | 2160  | 180  | 24 | 6 | — | — | 1 |
| OBSOLETE |  | 9360  | 2340  | 195  | 22 | 6 | — | — | 0 |
| OBSOLETE |  | 10080 | 2520  | 210  | 20 | 5 | — | — | 9 |
| OBSOLETE |  | 11520 | 2880  | 240  | 18 | 5 | — | — | 8 |
| OBSOLETE |  | 12960 | 3240  | 270  | 16 | 5 | — | — | 7 |
| OBSOLETE |  | 15120 | 3780  | 315  | 14 | 5 | — | — | 6 |
| OBSOLETE |  | 17280 | 4320  | 360  | 12 | 5 | — | — | 5 |
| OBSOLETE |  | 20880 | 5220  | 435  | 10 | 5 | — | — | 4 |
| OBSOLETE |  | 26640 | 6660  | 555  | 8  | 5 | — | — | 3 |
| OBSOLETE |  | 35280 | 8820  | 735  | 6  | 5 | — | — | 2 |
| OBSOLETE |  | 51840 | 12960 | 1080 | 4  | 5 | — | — | 1 |

|          |  |       |       |      |    |   |   |   |   |
|----------|--|-------|-------|------|----|---|---|---|---|
| OBSOLETE |  | 5040  | 1260  | 105  | 40 | 4 | — | — | 9 |
| OBSOLETE |  | 4320  | 1080  | 90   | 50 | 4 | — | — | 8 |
| OBSOLETE |  | 4320  | 1080  | 90   | 48 | 4 | — | — | 7 |
| OBSOLETE |  | 4320  | 1080  | 90   | 46 | 4 | — | — | 6 |
| OBSOLETE |  | 4320  | 1080  | 90   | 44 | 4 | — | — | 5 |
| OBSOLETE |  | 5040  | 1260  | 105  | 42 | 4 | — | — | 4 |
| OBSOLETE |  | 5040  | 1260  | 105  | 40 | 4 | — | — | 3 |
| OBSOLETE |  | 5040  | 1260  | 105  | 38 | 4 | — | — | 2 |
| OBSOLETE |  | 5760  | 1440  | 120  | 36 | 4 | — | — | 1 |
| OBSOLETE |  | 5760  | 1440  | 120  | 34 | 4 | — | — | 0 |
| OBSOLETE |  | 6480  | 1620  | 135  | 32 | 3 | — | — | 9 |
| OBSOLETE |  | 7200  | 1800  | 150  | 30 | 3 | — | — | 8 |
| OBSOLETE |  | 7200  | 1800  | 150  | 28 | 3 | — | — | 7 |
| OBSOLETE |  | 7920  | 1980  | 165  | 26 | 3 | — | — | 6 |
| OBSOLETE |  | 8640  | 2160  | 180  | 24 | 3 | — | — | 5 |
| OBSOLETE |  | 9360  | 2340  | 195  | 22 | 3 | — | — | 4 |
| OBSOLETE |  | 10080 | 2520  | 210  | 20 | 3 | — | — | 3 |
| OBSOLETE |  | 11520 | 2880  | 240  | 18 | 3 | — | — | 2 |
| OBSOLETE |  | 12960 | 3240  | 270  | 16 | 3 | — | — | 1 |
| OBSOLETE |  | 15120 | 3780  | 315  | 14 | 3 | — | — | 0 |
| OBSOLETE |  | 17280 | 4320  | 360  | 12 | 2 | — | — | 9 |
| OBSOLETE |  | 20880 | 5220  | 435  | 10 | 2 | — | — | 8 |
| OBSOLETE |  | 26640 | 6660  | 555  | 8  | 2 | — | — | 7 |
| OBSOLETE |  | 35280 | 8820  | 735  | 6  | 2 | — | — | 6 |
| OBSOLETE |  | 51840 | 12960 | 1080 | 4  | 2 | — | — | 5 |
| OBSOLETE |  | 4320  | 1080  | 90   | 50 | 2 | — | — | 4 |
| OBSOLETE |  | 4320  | 1080  | 90   | 48 | 2 | — | — | 3 |
| OBSOLETE |  | 4320  | 1080  | 90   | 46 | 2 | — | — | 2 |
| OBSOLETE |  | 4320  | 1080  | 90   | 44 | 2 | — | — | 1 |
| OBSOLETE |  | 5040  | 1260  | 105  | 42 | 2 | — | — | 0 |
| OBSOLETE |  | 5040  | 1260  | 105  | 40 | 1 | — | — | 9 |
| OBSOLETE |  | 5040  | 1260  | 105  | 38 | 1 | — | — | 8 |
| OBSOLETE |  | 5760  | 1440  | 120  | 36 | 1 | — | — | 7 |
| OBSOLETE |  | 5760  | 1440  | 120  | 34 | 1 | — | — | 6 |
| OBSOLETE |  | 6480  | 1620  | 135  | 32 | 1 | — | — | 5 |
| OBSOLETE |  | 7200  | 1800  | 150  | 30 | 1 | — | — | 4 |
| OBSOLETE |  | 7200  | 1800  | 150  | 28 | 1 | — | — | 3 |
| OBSOLETE |  | 7920  | 1980  | 165  | 26 | 1 | — | — | 2 |
| OBSOLETE |  | 8640  | 2160  | 180  | 24 | 1 | — | — | 1 |
| OBSOLETE |  | 9360  | 2340  | 195  | 22 | 1 | — | — | 0 |
| OBSOLETE |  | 10080 | 2520  | 210  | 20 | 0 | — | — | 9 |
| OBSOLETE |  | 11520 | 2880  | 240  | 18 | 0 | — | — | 8 |
| OBSOLETE |  | 12960 | 3240  | 270  | 16 | 0 | — | — | 7 |
| OBSOLETE |  | 15120 | 3780  | 315  | 14 | 0 | — | — | 6 |
| OBSOLETE |  | 17280 | 4320  | 360  | 12 | 0 | — | — | 5 |
| OBSOLETE |  | 20880 | 5220  | 435  | 10 | 0 | — | — | 4 |
| OBSOLETE |  | 26640 | 6660  | 555  | 8  | 0 | — | — | 3 |
| OBSOLETE |  | 35280 | 8820  | 735  | 6  | 0 | — | — | 2 |
| OBSOLETE |  | 51840 | 12960 | 1080 | 4  | 0 | — | — | 1 |

|                                                                                       |  |                                           |             |                                                                                                       |                 |
|---------------------------------------------------------------------------------------|--|-------------------------------------------|-------------|-------------------------------------------------------------------------------------------------------|-----------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>O.HU                               | 23-MAR-2006 |  TE Connectivity |                 |
|                                                                                       |  | CHK<br>S.HDU                              | 23-MAR-2006 |                                                                                                       |                 |
|                                                                                       |  | APVD<br>W.J.KE                            | 23-MAR-2006 |                                                                                                       |                 |
|                                                                                       |  | PRODUCT SPEC                              |             |                                                                                                       |                 |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED: |             | NAME                                                                                                  |                 |
|  |  | 0 PLC                                     | ± —         | AMPMODU 2.0mm PITCH,REC<br>CONN,VERTICAL,MOUNT TYPE                                                   |                 |
|                                                                                       |  | 1 PLC                                     | ± 0.15      |                                                                                                       |                 |
|                                                                                       |  | 2 PLC                                     | ± 0.10      |                                                                                                       |                 |
|                                                                                       |  | 3 PLC                                     | ± 0.05      |                                                                                                       |                 |
|                                                                                       |  | 4 PLC                                     | ± —         |                                                                                                       |                 |
|                                                                                       |  | ANGLES                                    | ± 3°        |                                                                                                       |                 |
| MATERIAL                                                                              |  | FINISH                                    |             |                                                                                                       |                 |
| SEE SHEET 1                                                                           |  | SEE SHEET 1                               |             |                                                                                                       |                 |
|                                                                                       |  | WEIGHT                                    | —           |                                                                                                       |                 |
|                                                                                       |  | CUSTOMER DRAWING                          |             |                                                                                                       |                 |
|                                                                                       |  |                                           |             | SIZE<br>A3                                                                                            | CAGE CODE<br>—  |
|                                                                                       |  |                                           |             | DRAWING NO<br>C-1734506                                                                               |                 |
|                                                                                       |  |                                           |             | RESTRICTED TO<br>—                                                                                    |                 |
|                                                                                       |  |                                           |             | SCALE<br>1:1                                                                                          | SHEET<br>2 OF 2 |
|                                                                                       |  |                                           |             | REV<br>B1                                                                                             |                 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1734506-2](#)