

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD




C

REVISED SHELL MATERIAL




18MAY2016

B.L

J.L



RECOMMENDED PCB LAYOUT (THICKNESS: 1.6MM)  
(DIMENSION TOLERANCE: 1 PLC: ±0.1 2PLC: ±0.05)



3.25		PBT	1-1734510-1
2.55		PBT	1734510-3
2.85		PA9T	1734510-2
2.85		PBT	1734510-1
DIM A	SOLERING PROCESS	HOUSING MATERIAL	PART NUMBER


NOTE:

- MATERIAL:  
HOUSING: (SEE TABLE) WITH 30% GF, UL 94V-0, COLOR BLACK.  
CONTACT: PHOSPHOR BRONZE, THICKNESS: 0.25mm.  
SHIELD: SUS304, THICKNESS: 0.40mm.
- FINISH:  
CONTACT: GOLD FLASH OVER  
0.762um [30u"] MIN. PALLADIUM-NICKEL PLATED ON CONTACT AREA,  
2.54um [100u"] MIN. MATTE TIN PLATED ON SOLDERTAILS,  
1.27um [50u"] MIN. NICKEL UNDERPLATED ALL OVER.  
SHIELD: 0.762um [30u"] MIN. MATTE TIN OVER 1.27um [50u"] MIN. Ni.  
UNDERPLATED ALL OVER.

- WAVE SOLDER CAPABLE TO 240°C. PER TE SPEC 109-202, CONDITION A.  
 WAVE SOLDER CAPABLE TO 265°C PER TE SPEC 109-202, CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
MM



MATERIAL  
SEE NOTE

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ± 0.5  
1 PLC ± 0.35  
2 PLC ± 0.25  
3 PLC ± 0.15  
4 PLC ± -  
ANGLES ± 3°

FINISH

SEE NOTE

DWN 20JAN2009

S. CHIEN

CHK 20JAN2009

S. CHIEN

APVD 20JAN2009

W. KODAMA

PRODUCT SPEC

108-57062

QUALIFICATION TEST REPORT

501-57070

WEIGHT 0.62 GRAMS

CUSTOMER DRAWING



TE Connectivity

NAME

MINI USB CONN., RCPT R/A, DIP, B TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1734510

SCALE

SHEET

1 of 2

REV

C

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

PVC

PAPER BOARD

TARY

TOTAL: 95 PCS.  
NET WEIGHT: 3.50 KGS.

PVC

CARTON

TOTAL: 4370 PCS.  
GROSS WEIGHT: 6.20 KGS.

30 REF

DETAIL A


HEIGHT : 8mm

DETAIL A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± -  
4 PLC ± -  
ANGLES ± -  
FINISH

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

MINI USB CONN., RCPT R/A, DIP, B TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779C=1734510

SCALE

SHEET

2 of 2

REV

C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1734510-2](#)