





DIMENSIONS IN MILLIMETERS DO NOT SCALE PRINT




RECOMMENDED PCB LAYOUT (TYPE A)
(TOLERANCE: ± 0.05)

NOTE:

1. MATERIAL:
HOUSING: THERMOPLASTIC WITH 33% GF, UL 94V-0, BLACK COLOR.
ACTUATOR: THERMOPLASTIC, UL 94V-0, BROWN COLOR.
CONTACTS: PHOSPHOR BRONZE.
TABS: BRASS.
2. FINISH:
CONTACTS: GOLD FLASH OVER $50\mu''$ MIN. NICKEL ON ENTIRE CONTACT.
△ CONTACTS: $30\mu''$ MIN. GOLD ON CONTACT AREA, WITH GOLD FLASH OVER
 $50\mu''$ MIN. NICKEL ON ENTIRE CONTACT.
TABS: $120\mu''$ MIN. MATTE-TIN OVER $50\mu''$ MIN. NICKEL.
3. REFLOW SOLDER CAPABLE TO 260°C AS PER **TE CONNECTIVITY**
SPEC. 109-201, CONDITION B.
4. NO TYCO LOGO AND DATE CODE ON THE PRODUCT.



RECOMMENDED FFC LAYOUT






RECOMMENDED FPC LAYOUT

△_a

0.34g	17.70	16.90	12.65	11.50	24	6-1734742-0
0.52g	25.70	24.90	20.65	19.50	40	4-1734742-0
0.51g	25.20	24.40	20.15	19.00	39	3-1734742-9
0.50g	24.70	23.90	19.65	18.50	38	3-1734742-8
0.49g	24.20	23.40	19.15	18.00	37	3-1734742-7
0.48g	23.70	22.90	18.65	17.50	36	3-1734742-6
0.46g	23.20	22.40	18.15	17.00	35	3-1734742-5
0.45g	22.70	21.90	17.65	16.50	34	3-1734742-4
0.44g	22.20	21.40	17.15	16.00	33	3-1734742-3
0.43g	21.70	20.90	16.65	15.50	32	3-1734742-2
0.42g	21.20	20.40	16.15	15.00	31	3-1734742-1
0.41g	20.70	19.90	15.65	14.50	30	3-1734742-0
0.40g	20.20	19.40	15.15	14.00	29	2-1734742-9
0.39g	19.70	18.90	14.65	13.50	28	2-1734742-8
0.38g	19.20	18.40	14.15	13.00	27	2-1734742-7
0.37g	18.70	17.90	13.65	12.50	26	2-1734742-6
0.36g	18.20	17.40	13.15	12.00	25	2-1734742-5
0.34g	17.70	16.90	12.65	11.50	24	2-1734742-4
0.33g	17.20	16.40	12.15	11.00	23	2-1734742-3
0.32g	16.70	15.90	11.65	10.50	22	2-1734742-2
0.31g	16.20	15.40	11.15	10.00	21	2-1734742-1
0.30g	15.70	14.90	10.65	9.50	20	2-1734742-0
0.29g	15.20	14.40	10.15	9.00	19	1-1734742-9
0.28g	14.70	13.90	9.65	8.50	18	1-1734742-8
0.27g	14.20	13.40	9.15	8.00	17	1-1734742-7
0.26g	13.70	12.90	8.65	7.50	16	1-1734742-6
0.25g	13.20	12.40	8.15	7.00	15	1-1734742-5
0.24g	12.70	11.90	7.65	6.50	14	1-1734742-4
0.22g	12.20	11.40	7.15	6.00	13	1-1734742-3
0.21g	11.70	10.90	6.65	5.50	12	1-1734742-2
0.20g	11.20	10.40	6.15	5.00	11	1-1734742-1
0.19g	10.70	9.90	5.65	4.50	10	1-1734742-0
0.18g	10.20	9.40	5.15	4.00	9	1734742-9
0.17g	9.70	8.90	4.65	3.50	8	1734742-8
0.16g	9.20	8.40	4.15	3.00	7	1734742-7
0.15g	8.70	7.90	3.65	2.50	6	1734742-6
WEIGHT	D	C	B	A	NO. OF CONTACTS	PART NUMBER
	DIMENSIONS					

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.2 2 PLC ±0.1 3 PLC ±0.05 ANGLES ±3'		DWN		A. WU		 TE Connectivity					
				01-DEC-2005							
				CHK		S. HOU		NAME			
						01-DEC-2005					
MATERIAL SEE NOTE		APVD		W.J. KE		FPC/FFC CONN., 0.5 MM PITCH, ZIF, VERTICAL, SMT, TYPE A					
				01-DEC-2005							
		PRODUCT SPEC									
		108-57324									
FINISH SEE NOTE		QUALIFICATION TEST REPORT		LOC		SIZE		DRAWING NO		REV	
		501-57364		DW		A ₃		C-1734742		P	
		WEIGHT		SCALE				SHEET			
		-				--				1 OF 2	

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT.



1000	4	4000	44.0	40.40	4.61	2.08	40
					4.57	2.04	39
					4.53	2.00	38
					4.49	1.96	37
					4.45	1.92	36
					4.37	1.84	35
					4.33	1.80	34
					4.29	1.76	33
					4.25	1.72	32
					4.21	1.68	31
1000	6	6000	32.0	28.40	6.05	2.46	30
					5.99	2.40	29
					5.93	2.34	28
					5.87	2.28	27
					5.81	2.22	26
					5.75	2.16	25
					5.63	2.04	24
					5.57	1.98	23
					5.51	1.92	22
					5.45	1.86	21
1000	7	7000	24.0	20.40	5.58	2.10	20
					5.51	2.03	19
					5.44	1.96	18
					5.37	1.89	17
					5.30	1.82	16
					5.23	1.75	15
					5.16	1.68	14
					5.02	1.54	13
					4.95	1.47	12
					4.88	1.40	11
1000	8	8000	20.0	16.40	4.81	1.33	10
					4.74	1.26	9
					4.67	1.19	8
					4.60	1.12	7
					4.53	1.05	6
PCS/REEL	REELS/CARTON	QUANTITY	DIM W	DIM X	G/W (KG)	N/W (KG)	NO. OF CONTACTS

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- ANGLES ±-	DWN	A. WU 01-DEC-2005		 TE Connectivity			
	CHK	S. HOU 01-DEC-2005					
	MATERIAL	APVD	W.J. KE 01-DEC-2005		FPC/FFC CONN., 0.5 MM PITCH, ZIF, VERTICAL, SMT, TYPE A		
	-	PRODUCT SPEC					
FINISH	APPLICATION SPEC		LOC	SIZE	DRAWING NO	REV	
	WEIGHT		DW	A ₃	C-1734742	P	
		SCALE			SHEET		
		--			2 OF 2		

LTR	REVISION RECORD	SEE SHEET 1.	ECO	DWN	CHK	DATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1734742-4](#)