







NOTES:

1 MATERIAL:
HOUSING: GLASS FILLED HIGH TEMP NYLON, NATURAL COLOR (BEIGE)
CONTACT: PHOSPHOR BRONZE

2 FINISH: MATTE TIN OVER NICKEL UNDERPLATE

3. PACKAGING: TAPE & REEL (PACKAGING SPEC: 107-51189)



RECOMMENDED PCB LAYOUT
(FOR ODD POSITION CONNECTORS)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES $\pm 3^\circ$
MATERIAL	FINISH
1	2

DWN	WYLEE	25JUN04
CHK	LP TAN	
APVD	SF LEONG	
PRODUCT SPEC	108-51054	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

Tyco Electronics Corporation Singapore	
NAME	ON TAPING (EMBOSS) ASSY, 1.00mm FFC CONN. WITH KAPTON TAPE SMT, V, (NON-ZIF)
SIZE	A3
CAGE CODE	00779
DRAWING NO	C-1735042
SCALE	2:1
SHEET	1
OF	1
REV	L

29.00	32.00	31.00	31.00	10.0	30	3-	-0
28.00	31.00	30.00	30.00		29	2-	-9
27.00	30.00	29.00	29.00		28	2-	-8
26.00	29.00	28.00	28.00		27	2-	-7
25.00	28.00	27.00	27.00		26	2-	-6
24.00	27.00	26.00	26.00		25	2-	-5
23.00	26.00	25.00	25.00		24	2-	-4
22.00	25.00	24.00	24.00		23	2-	-3
21.00	24.00	23.00	23.00		22	2-	-2
20.00	23.00	22.00	22.00		21	2-	-1
19.00	22.00	21.00	21.00	8.0	20	2-	-0
18.00	21.00	20.00	20.00		19	1-	-9
17.00	20.00	19.00	19.00		18	1-	-8
16.00	19.00	18.00	18.00		17	1-	-7
15.00	18.00	17.00	17.00		16	1-	-6
14.00	17.00	16.00	16.00		15	1-	-5
13.00	16.00	15.00	15.00		14	1-	-4
12.00	15.00	14.00	14.00		13	1-	-3
11.00	14.00	13.00	13.00		12	1-	-2
10.00	13.00	12.00	12.00		11	1-	-1
9.00	12.00	11.00	11.00	5.0	10	1-	-0
8.00	11.00	10.00	10.00		9		-9
7.00	10.00	9.00	9.00		8		-8
6.00	9.00	8.00	8.00		7		-7
5.00	8.00	7.00	7.00		6		-6
4.00	7.00	6.00	6.00		5		-5
3.00	6.00	5.00	5.00		4		-4
H	G	F	E	D	POS.	ON TAPE PART NO.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1735042-8](#)