






D

C

B

A



RECOMMENDED PCB LAYOUT
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±0.20
3 PLC	±
4 PLC	±
ANGLES	±3°
FINISH	

MATERIAL

-

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

SATA BACKPLANE RECEPTACLE,
VERTICAL, SMT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779C-1735284

SCALE

4:1

SHEET


2

OF

5



REV

D




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

T&R FOR LOW PROFILE



- NOTES:
1. PACKAGING QUANTITY: 550 PCS PER REEL.
 2. REEL: $\varnothing 380$ - $\varnothing 100$ HUB-89W(72.4W INSIDE).





DETAIL C
SCALE 8:1

SECTION B-B


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
		CHK				
DIMENSIONS:		APVD	NAME SATA BACKPLANE RECEPTACLE, VERTICAL, SMT			
mm		PRODUCT SPEC				
		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	A2		C-1735284	-
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING				
0 PLC ±		SCALE 2:1				
1 PLC ±		SHEET 4 OF 5				
2 PLC ±0.3		REV D				
3 PLC ±						
4 PLC ±						
ANGLES ±5°						
FINISH						

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

T&R FOR STANDARD PROFILE



- NOTES:
1. PACKAGING QUANTITY: 450 PCS PER REEL.
 2. REEL: $\varnothing 380$ - $\varnothing 100$ HUB-89W(72.4W INSIDE).



DETAIL D
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
		CHK				
DIMENSIONS:		APVD	NAME SATA BACKPLANE RECEPTACLE, VERTICAL, SMT			
mm		PRODUCT SPEC				
		APPLICATION SPEC	SIZE A2			
		WEIGHT	CAGE CODE C-1735284			
MATERIAL		CUSTOMER DRAWING	DRAWING NO C-1735284			
			RESTRICTED TO			
			SCALE 2:1 SHEET 5 OF 5 REV D			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1735284-5](#)