



- 1 CONTACT: COPPER ALLOY PER ASTM B196 OR LEADED NICKEL COPPER C97.
SLEEVE: STAINLESS STEEL PER AISI 305
- 2 CONTACT: 1.27µm MIN GOLD PER ASTM B488 OVER 2.54µm
MIN NICKEL PER QQ-N-290 ON ENTIRE STOCK.
- SLEEVE: PASSIVATED
- 3 OPTIONAL ALTERNATE MARKING: LETTER "S"
- 4 GREEN COLOR BAND.
5. APPLICABLE WIRE SIZE: 22-24-26 AWG
WIRE INSULATION DIAMETER: 1.4 MAX
INSULATION STRIP LENGTH: 3.08-3.58
6. APPLICATION TOOLING:
CRIMPING TOOL: TYCO PART NUMBER 601966-1 (M22520/2-01)
POSITIONER: TYCO PART NUMBER 601966-8 (M22520/2-23)
SELECTOR POSITION: AWG 22: 4
AWG 24: 3
AWG 26: 3
CONTACT INSERTION/EXTRCTION TOOL: 91066-1 (M81969/1-01)
7. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738008-1](#)