


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	00		0	CONVERTED RADIAL DWG TO TYCO ACAD DWG	11/03	—	—
			1	REVISED	22APR10	RF	JM

1 FRONT & REAR INSULATORS: THERMOSET EPOXY PER ASTM D5948
CONTACT RETENTION CLIPS: COPPER ALLOY PER ASTM B194
REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B, EXCEPT 4.6.6.1




2 DATE CODE: YEAR & WEEK (YY WW)

3. DESCRIPTIVE PART NUMBER: GPRBE20C1PA
THIS INSERT CONTAINS:
19 CAVITIES FOR SIZE 20 PIN CONTACTS
1 CAVITY FOR SIZE 5 PIN CONTACTS

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS
UNDER A LICENSE FROM RADIAL SA.




MATING FACE



THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

1738136-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R FLAIG NOV03		 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK J MOSIER NOV03					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J MOSIER NOV03		NAME	
		0 PLC ± -		PRODUCT SPEC		GPR-B PIN INSERT CLASS E CONTACT ARRANGEMENT 20C1 KEY A	
		1 PLC ± -		—			
		2 PLC ± 0.05 [.002]		APPLICATION SPEC			
		3 PLC ± -		—			
4 PLC ± -		ANGLES ± -		FINISH		SIZE	
MATERIAL		—		WEIGHT		CAGE CODE	
1				—		DRAWING NO	
				CUSTOMER DRAWING		RESTRICTED TO	
						A2 00779 C=1738136	
						SCALE	
						1:1	
						SHEET	
						1 of 1	
						REV	
						1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738136-1](#)