





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY - ALL RIGHTS RESERVED



## MATING FACE



THIS PRODUCT HAS NOT COMPLETED  
VALIDATION TESTING

**FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.  
CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194  
REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.**

2 PART TO BE MARKED WITH THE IDENTIFICATION, THE PART NO.  
AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.

3. THIS INSERT CONTAINS: 16 CAVITIES FOR SIZE 20 PIN CONTACTS  
6 CAVITIES FOR SIZE 16 PIN CONTACTS

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALL SA.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 10-7-10	 TE Connectivity			
DIMENSIONS:		CHK K. HOGAN 10-7-10				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD K. HOGAN 10-7-10				
 0 PLC ±- 1 PLC ±- 2 PLC ±0.05 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC - APPLICATION SPEC -				
MATERIAL	FINISH	WEIGHT	NAME INSERT ASSEMBLY, PIN, ARRANGEMENT 22, KEY A, GPRB			
 -		SIZE A2	CAGE CODE 00779	DRAWING NO C-1738146	RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV B

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738146-3](#)