

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	FREE STATE DIMENSION UPDATED	27JUN2019	MB	PKS




- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 10.41±0.08 [.410±.003] CENTERS.
- 2 SLOT ACCEPTS 1.15–1.29mm [#17–#16] AWG COPPER MAGNET WIRE. 2 WIRES OF THE SAME SIZE AND TYPE MAX PER SLOT.
- 3 CONTACT LEAF ACCEPTS 0.81 [.032] THICK POKE-IN TAB, (REFERENCE TAB DRAWING 1217324).
- 4 0.002032 [.000080] MIN TIN PLATE OVER 0.00127 [.000050] MIN NICKEL UNDERPLATE.

D

C

B

A



D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN VJAI 23JAN2018		 TE Connectivity				
			CHK VJAI 23JAN2018						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SENTHIL 23JAN2018		NAME SPECIAL LEAF CONTACT, 500 SERIES MAG-MATE —			
		0 PLC ± — 1 PLC ± — 2 PLC ± 0,25[.010] 3 PLC ± — 4 PLC ± — ANGLES ± ± —		PRODUCT SPEC 108-2053 APPLICATION SPEC 114-2066					
MATERIAL 4M BRASS		FINISH — 		WEIGHT 0.000000		SIZE A2	CAGE CODE 00779	DRAWING NO C-1742203	RESTRICTED TO —
CUSTOMER DRAWING						SCALE 10:1		SHEET 1 of 1	REV C

1742203

1742203-1

PART NUMBER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1742203-1](#)