

REV. 10/83

PRINT DIST

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT


METRIC

三角法 (3rd ANGLE PROJECTION)


番号 (No.)

C-175062




断面 C-C
SECT.



断面 B-B
SECT.



△ (接触面のみ)
CONTACT SIDE ONLY
断面 A-A
SECT.



注: △ 部分金めっき

NOTES:
△ SELECTIVE GOLD

173581-2	SELECTIVE GOLD 部分金めっき	175062-2
173581-1	PRE-TINNED 錫めっき済	175062-1
通線端子型番	FINISH	仕上げ
Strip No.		PART NO. 製品型番

AMP

Tokyo, Japan

AMP (NAME)
.040 SERIES RECEPTACLE CONTACT (LOOSE PIECE)
.040 シリ-ズ リセプタクル (部品)

一般公差 (GENERAL TOLERANCES)
寸法 (DIMENSIONS): ±0.25
穴径 (HOLE DIA.): ±0.25
半径 (RADIUS): ±0.25
角度 (ANGLE): ±3°

寸法 (DIMENSIONS)
SIZE LOC 番号 (No.)
A3 J C-175062

尺規 (SCALED) REV. 0 SHEET 1 OF 1

Copyright © 1992 AMP CORP., LTD. ALL RIGHTS RESERVED.	Copyright © 1992 AMP CORP., LTD. ALL RIGHTS RESERVED.
特許電線端子型番 (WIRE RANGE) 0.3-0.56mm (AWG#22-#20)	絶縁外皮 (INSULATION DIA.) 1.8-2 mmφ
材料 (MATERIAL) KLF-5, 板厚: 0.25	仕上げ (FINISH) SEE TABLE
DR. Y. Minoda	DE. C. Angino
CHK. M. Osada	DATE 5/27/92
LTR 変更 (REVISION RECORD)	DR CHK DATE

CUSTOMER DRAWING 参考図面

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[175062-1](#)