



| | | | | | | | |
|----------|------------------|-----------------|------------------|-------------------|------------------|----------------|-----------|
| OBSOLETE | 78.74 [3.100] | 31 | 86.36 [3.400] | 100.33 [3.950] | 64 | 1-1761685-7 | |
| | 73.66 [2.900] | 29 | 81.28 [3.200] | 95.25 [3.750] | 60 | 1-1761685-6 | |
| | 60.96 [2.400] | 24 | 68.58 [2.700] | 82.55 [3.250] | 50 | 1-1761685-5 | |
| | 53.34 [2.100] | 21 | 60.96 [2.400] | 74.93 [2.950] | 44 | 1-1761685-4 | |
| | 48.26 [1.900] | 19 | 55.88 [2.200] | 69.85 [2.750] | 40 | 1-1761685-3 | |
| OBSOLETE | 43.18 [1.700] | 17 | 50.80 [2.000] | 64.77 [2.550] | 36 | 1-1761685-2 | |
| | 40.64 [1.600] | 16 | 48.26 [1.900] | 62.23 [2.450] | 34 | 1-1761685-1 | |
| | 35.56 [1.400] | 14 | 43.18 [1.700] | 57.15 [2.250] | 30 | 1-1761685-0 | |
| | 30.48 [1.200] | 12 | 38.10 [1.500] | 52.07 [2.050] | 26 | 1761685-9 | |
| | 27.94 [1.100] | 11 | 35.56 [1.400] | 49.53 [1.950] | 24 | 1761685-8 | |
| | 22.86 [.900] | 9 | 30.48 [1.200] | 44.45 [1.750] | 20 | 1761685-7 | |
| | 17.78 [.700] | 7 | 25.40 [1.000] | 39.37 [1.550] | 16 | 1761685-6 | |
| | OBSOLETE | 15.24 [.600] | 6 | 22.86 [.900] | 36.83 [1.450] | 14 | 1761685-5 |
| | | 12.70 [.500] | 5 | 20.32 [.800] | 34.29 [1.350] | 12 | 1761685-4 |
| | | 10.16 [.400] | 4 | 17.78 [.700] | 31.75 [1.250] | 10 | 1761685-3 |
| | D | C | B | A | NO OF POS | PART NUMBER | |

| | | | | | | | | | | | | | | | | | | |
|--|--|--|--|--|--|--|--|--------|--|------------------------------|--|---------------------------|--|-----------|------------|---------------|-----|---|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | | | | | OWN D. CRISAMORE/DIT | | OSUNDS | | Tyco Electronics Corporation | | Harrisburg, PA 17105-3608 | | | | | | |
| | | | | | | COW S.BOLASH | | OSUNDS | | NAME | | Tyco Electronics | | | | | | |
| DIMENSIONS: mm [INCHES] | | | | | | TOLERANCES UNLESS OTHERWISE SPECIFIED: | | | | | | APPROV'D M.WALMSLEY | | | | | | |
| | | | | | | PLC ± — | | | | | | PRODUCT SPEC | | | | | | |
| | | | | | | PLC ± — | | | | | | — | | | | | | |
| | | | | | | PLC ± 0.13[.005] | | | | | | APPLICATION SPEC | | | | | | |
| | | | | | | PLC ± — | | | | | | — | | | | | | |
| ANGLES FINISH | | | | | | WEIGHT | | | | | | SIZE | | CAGE CODE | DRAWING NO | RESTRICTED TO | | |
| | | | | | | — | | | | | | A1 | | 00779 | C=1761685 | — | | |
| | | | | | | CUSTOMER DRAWING | | | | | | SCALE | | 4:1 | SHEET | 1 OF 1 | REV | C |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1761685-3](#)