


| REVISIONS | | | | | |
|-----------|-----|---------------------------|-----------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | 3 | REVISED PER ECR-20-010947 | 04AUG2020 | GK | KA |



NOTE:

1 FOR PART NUMBERS SEE SHEET 3 OF 3.

2 MARK SHOULD BE CENTRALLY POSITIONED ±0.1mm.

3 WIDTH OF MARK DEPENDS ON CHARACTER PRINTED

| | | | | | |
|--|--|------------------------------------|--|--------------------|---------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN RAGHAVENDRA K 25MAR2013 | TE Connectivity | | |
| | | CHK KEAN ALAN 25MAR2013 | | | |
| DIMENSIONS: mm | | APVD MARIO APPELLO 25MAR2013 | NAME SNAP-ON MARKER STB/STD SIZE 12 WITH APPLICATOR | | |
| | | PRODUCT SPEC | — | | |
| | | APPLICATION SPEC | — | | |
| MATERIAL — | | WEIGHT — | SIZE A3 | CAGE CODE C2290 | DRAWING NO C-1768045-1 |
| | | CUSTOMER DRAWING | | SCALE NTS | SHEET 1 OF 3 |
| | | | | REV 3 | |





REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
| | — | SEE SHEET 1 | — | — | — |

4

OBSOLETE PART

| | | | | | |
|---|--|--|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN 25MAR2013 RAGHAVENDRA K | | <div> TE Connectivity</div> | |
| | | CHK 25MAR2013 KEAN ALAN | | | |
| DIMENSIONS: mm | | TOLERANCES UNLESS OTHERWISE SPECIFIED: | | NAME | |
|  | | 0 PLC ± — | | PRODUCT SPEC | |
| | | 1 PLC ± — | | APPLICATION SPEC | |
| | | 2 PLC ± — | | — | |
| MATERIAL — | | 3 PLC ± — | | SIZE | |
| | | 4 PLC ± — | | CAGE CODE | |
| | | ANGLES ± — | | DRAWING NO | |
| FINISH — | | WEIGHT — | | RESTRICTED TO | |
| CUSTOMER DRAWING | | | | SCALE NTS | |
| | | | | SHEET 3 OF 3 | |
| | | | | REV 3 | |

| DESCRIPTION | PART NO. |
|------------------------|------------------------|
| STB12-0-0 | 4-1768039-4 |
| STB12-1-1 | 4-1768039-5 |
| STB12-2-2 | 4-1768039-6 |
| STB12-3-3 | 4-1768039-7 |
| STB12-5-5 | 4-1768039-8 |
| STB12-6-6 | 4-1768039-9 |
| STB12-7-7 | 5-1768039-0 |
| STB12-8-8 | 5-1768039-1 |
| STB12-BLANK-0 | 5-1768039-2 |
| STB12-BLANK-1 | 5-1768039-3 |
| STB12-BLANK-2 | 5-1768039-4 |
| STB12-BLANK-3 | 5-1768039-5 |
| STB12-BLANK-5 | 5-1768039-6 |
| STB12-BLANK-6 | 5-1768039-7 |
| STB12-BLANK-7 | 5-1768039-8 |
| STB12-BLANK-8 | 5-1768039-9 |
| STD12W/1-12 | 7-1768403-0 |
| STD12W-0 | 027608-000 |
| STD12W-1 | 028690-000 |
| STD12W-2 | 127922-000 |
| STD12W-3 | 869998-000 |
| STD12W-4 | 422284-000 |
| STD12W-5 | 329976-000 |
| STD12W-6 | 654200-000 |
| STD12W-7 | 727782-000 |
| STD12W-8 | 157886-000 |
| STD12W-9 | 612832-000 |
| STD12W-A | 392758-000 |
| STD12W-AC | 8-1768044-0 |
| STD12W-B | 190370-000 |
| STD12W-BLANK | 8-1768044-2 |
| STD12W-C | 379242-000 |
| STD12W-COLON | 227492-000 |
| STD12W-D | 466552-000 |
| STD12W-D-LC | 8-1768044-4 |
| STD12W-DOT | 8-1768044-5 |
| STD12W-E | 952178-000 |

| DESCRIPTION | PART NO. |
|--------------|-------------|
| STD12W-EARTH | 8-1768044-6 |
| STD12W-F | 242654-000 |
| STD12W-G | 371912-000 |
| STD12W-H | 544882-000 |
| STD12W-I | 743644-000 |
| STD12W-J | 925236-000 |
| STD12W-K | 402858-000 |
| STD12W-L | 372210-000 |
| STD12W-M | 797170-000 |
| STD12W-MINUS | 9-1768044-3 |
| STD12W-N | 224378-000 |
| STD12W-P | 200490-000 |
| STD12W-PLUS | 9-1768044-6 |
| STD12W-Q | 881472-000 |
| STD12W-R | 610526-000 |
| STD12W-S | 958362-000 |
| STD12W-SLASH | 102828-000 |
| STD12W-T | 080248-000 |
| STD12W-U | 606344-000 |
| STD12W-V | 244058-000 |
| STD12W-W | 922324-000 |
| STD12W-X | 151660-000 |
| STD12W-Y | 976192-000 |
| STD12W-Z | 928688-000 |
| STD12Y-0 | 9-1768044-8 |
| STD12Y-1 | 9-1768044-9 |
| STD12Y-2 | 1768045-1 |
| STD12Y-3 | 1768045-2 |
| STD12Y-4 | 1768045-3 |
| STD12Y-5 | 1768045-4 |
| STD12Y-6 | 1768045-5 |
| STD12Y-7 | 1768045-6 |
| STD12Y-8 | 1768045-7 |
| STD12Y-9 | 1768045-8 |
| STD12Y-A | 1768045-9 |
| STD12Y-AC | 1-1768045-0 |
| STD12W/1-48 | 8-1768710-0 |

| DESCRIPTION | PART NO. |
|------------------------|------------------------|
| STD12Y-B | 1-1768045-2 |
| STD12Y-BLANK | 1-1768045-3 |
| STD12Y-C | 1-1768045-5 |
| STD12Y-COLON | 1-1768045-6 |
| STD12Y-D | 1-1768045-7 |
| STD12Y-DOT | 1-1768045-9 |
| STD12Y-E | 2-1768045-0 |
| STD12Y-EARTH | 2-1768045-1 |
| STD12Y-F | 2-1768045-3 |
| STD12Y-G | 2-1768045-5 |
| STD12Y-G-LC | 2-1768045-6 |
| STD12Y-H | 2-1768045-7 |
| STD12Y-I | 2-1768045-9 |
| STD12Y-J | 3-1768045-0 |
| STD12Y-K | 3-1768045-1 |
| STD12Y-L | 3-1768045-3 |
| STD12Y-M | 3-1768045-5 |
| STD12Y-MINUS | 3-1768045-6 |
| STD12Y-N | 3-1768045-8 |
| STD12Y-P | 4-1768045-0 |
| STD12Y-PLUS | 4-1768045-1 |
| STD12Y-Q | 4-1768045-2 |
| STD12Y-R | 4-1768045-3 |
| STD12Y-S | 4-1768045-5 |
| STD12Y-SLASH | 4-1768045-6 |
| STD12Y-T | 4-1768045-7 |
| STD12Y-U | 4-1768045-8 |
| STD12Y-V | 4-1768045-9 |
| STD12Y-W | 5-1768045-0 |
| STD12Y-X | 5-1768045-1 |
| STD12Y-Y | 5-1768045-2 |
| STD12Y-Z | 5-1768045-3 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[797170-000](#)