

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	CUTTING BURR DETAILS ADDED	19NOV2018	RK	PS

1. MATERIAL:
HOUSING: POLYAMIDE 6 UL94V-2.
COLOR: NATURAL (OFF WHITE).
TUBULAR CONTACT: BRASS, TIN PLATED.
SCREW: M4, STEEL, ZINC PLATED W/ NON-
HEXAVALENT CHROMATE (CHROME III).
WIRE PROTECTOR: STAINLESS STEEL.
2. CURRENT RATING: 40A, 300V (UL).
55A, 300V (CSA).
WIRE RANGE: 8-18 AWG.
3. CONTINUOUS WORKING TEMPERATURE 100°C MAX.
- 4 CUTTING PROJECTION CAN BE ON BOTH SIDES
DEPENDING ON CUTTING LOCATION
5. CUTTING BURR MAX. 1mm ALLOWED.



1776311-4 AS SHOWN

	135.0	157.9	12	TSB150012DS	1-1776311-2
	121.5	144.4	11	TSB150011DS	1-1776311-1
	108.0	130.9	10	TSB150010DS	1-1776311-0
	94.5	117.9	9	TSB150009DS	1776311-9
	81.0	103.9	8	TSB150008DS	1776311-8
OBSOLETE	67.5	90.4	7	TSB150007DS	1776311-7
	54.0	76.9	6	TSB150006DS	1776311-6
	40.5	63.4	5	TSB150005DS	1776311-5
	27.0	49.9	4	TSB150004DS	1776311-4
	13.5	36.4	3	TSB150003DS	1776311-3
	-	22.9	2	TSB150002DS	1776311-2
	-	9.4	1	TSB150001DS	1776311-1
	DIM B	DIM A	POSN	CATALOG NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 3/21/05	TE Connectivity Ltd.		
		CHK C RICHARD 3/21/05			
DIMENSIONS: mm		APVD C RICHARD 3/21/05	NAME 13.5MM PITCH W/ WIRE PROTECTOR EUROPA TERMINAL BLOCK		
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL SEE NOTES		WEIGHT	SIZE A3	CAGE CODE 00779	RESTRICTED TO -
		FINISH SEE NOTES	DRAWING NO C=1776311		
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1776311-2](#)