




NOTE

1 MATERIAL:GLASS FIELD THERMO PLASTIC,POLYESTER
COLOR:BLACK

2 TO COAT ALL SURFACE OF HOUSING WITH TEFLON

注記

1 材料：ガラス入り熱可塑性ポリエステル樹脂
色：黒色

△ハウジング全面にテフロン塗装のこと

		10 POS.	53.43	47.83	43.37	34.29	9	2-178288-8
		10 POS.	53.43	47.83	43.37	34.29	9	1-178288-8
		8 POS.	45.81	40.12	35.97	26.67	7	1-178288-7
		6 POS.	38.19	32.59	28.13	19.05	5	2-178288-6
		6 POS.	38.19	32.59	28.13	19.05	5	1-178288-6
		5 POS.	34.38	28.78	24.32	15.24	4	1-178288-5
		4 POS.	30.57	24.97	20.51	11.43	3	2-178288-4
		4 POS.	30.57	24.97	20.51	11.43	3	1-178288-4
OBSOLETE		3 POS.	26.76	21.16	16.7	7.62	2	6-178288-3
OBSOLETE		3 POS.	26.76	21.16	16.7	7.62	2	5-178288-3
		3 POS.	26.76	21.16	16.7	7.62	2	2-178288-3
		3 POS.	26.76	21.16	16.7	7.62	2	1-178288-3
	FINISH	POS. DIMENSION	A	B	C	D	N	PART NUMBER

					 TE Connectivity	
					名称 (NAME) REC HSG FOR DYNAMIC, SINGLE ROW ダイナミック 3100リセハウジング	
					一般公差 (GENERAL TOLERANCE) 10以下 : ±0.2 10を超え 30以下 : ±0.25 30を超え 100以下 : ±0.3 角 度 : ±3°	
					SIZE LOC 番号 (No.) A3 J C-178288	
					尺 度 (SCALE) 2-1	
					REV. E4 SHEET 1 OF 2	
E4	REVISED PER ECO-11-005030	RK	HMR	21MAR11	DR. 9 JUL 91 N. Matsubara	DE. 9 JUL 91 N. Matsubara
LTR	変更 (REVISION RECORD)	DR	CHK	DATE	CHK. 17 JUL 91 N. Matsubara	APP. 17-DEC-'91 N. Matsubara

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-178288-6](#)