





- 注記:
1. 適用製品規格 : 108-5437
 2. 適用コンタクト型番 :
179973-0 , 179974-0 , 179975-0
 4. 取扱説明書 : 411-5691
- NOTES:
1. PRODUCT SPEC; 108-5437
 2. APPLICABLE CONTACT P/N
179973-0 , 179974-0 , 179975-0
 3. INSTRUCTION SHEET; 411-5691



断面 "A" - "A"
SECT.



自然色	(NATURAL)	7-179970-1
黒	(BLACK)	179970-9
青	(BLUE)	179970-6
黄	(YELLOW)	179970-4
赤	(RED)	179970-2
自然色	(NATURAL)	179970-1
色調	(COLOR)	型番 (P/N)

B6	REVISED ECR-18-014304	S.T	T.D	1998P 2018
B5	REVISED ECR-13-000284	L.L	F.M	08JAN 2013
B4	REVISED ECR-12-018436	L.L	F.M	23OCT 2012
B3	REVISED	K.S	N.Y	15JUN 2012
LTR	変更 (REVISION RECORD)	DR	CHK	DATE

絶縁電線断面積 (WIRE RANGE)	絶縁外径 (INSULATION DIA.)	名称 (NAME)
mm ² (AWG -)	4.3 MAX mmφ	"250" SERIES POSITIVE LOCK-EX-II 1Pos REC HSG "250"シリーズ・ポジティブロック-EX-II 極リセ・ハウジング
材料 (MATERIAL)	仕上 (FINISH)	一般公差 (GENERAL TOLERANCE)
6/6ナイロン 6/6NYLON		10mmT : ±0.2 10mmR, 30mmT : ±0.25 30mmR, 100mmT : ±0.3 角 度 : ±3°
DR. 30.JUN.'94 N. NAGASHIMA	DE. 4.JUL.'94 M. SUZUKI	10mmT : ±0.2 10mmR, 30mmT : ±0.25 30mmR, 100mmT : ±0.3 角 度 : ±3°
CHK. 4.JUL.'94 M. SHINDO	APP. 4.JUL.'94 Y. KASHIWA	
LDC		番号 (No.)
B J		179970
尺度 (SCALE)		REV. B7
5:1		SHEET 1 OF 1

(CUSTOMER DRAWING) 参 考 面

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[179970-9](#)