





REVISIONS 変更					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED PER ECO-20-007218	27MAY2020	C.X	D.Z




- NOTES;
1. GENERAL TOLERANCE: $\pm 0.3, \pm 3^\circ$
 2. MATERIA L: 66NYLON GF (UL94V-0)
 3. MATING CONN.P/N: SEE TABLE
 - ④ APPLICABLE P.C.B HOLE DIA: ϕA
PACHED HOLE: 0.7 ± 0.1
DRILLED HOLE: 0.8 ± 0.05
- ④ PRELIMINARY PARTS NOT FOR PRODUCTION.



番号 NO.	名称 NAME	材料 MATERIAL
①	ポストコンタクト POST CONTACT	黄銅 錫めっき仕上 BRASS, TIN PLATING
②	ヘッダーハウジング HDR HOUSING	66ナイロン・ガラス強化 UL94V-0 66NYLON GF UL94V-0

20POS.0CB.LAYOUT



3-1827228-6	20	YELLOW	④ 3-1827229-6
2-1827228-6	20	BLUE	④ 2-1827229-6
1-1827228-6	20	RED	④ 1-1827229-6
1827228-6	20	NATURAL	1827229-6
かん合相手側型番 (MATING CONN P/N)	極数 (POS)	色調 (COLOR)	型番 (P/N)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SATO 07APR2005	 TE Connectivity	
DIMENSIONS: 単位: 耗 mm		CHK T.HATANO 7APR2005		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD N.YAMASAKI 7APR2005	NAME 名称	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 製品規格 108-78229	GRACE INERTIA CONNECTOR 2.0 HDR ASSY	
MATERIAL 材料 SEE NOTE		APPLICATION SPEC 取付適用規格 114-5359		
FINISH 仕上		WEIGHT 0.000000	SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING		DRAWING NO 番号 C-1827229	RESTRICTED TO —	
SCALE 尺度 4:1		SHEET 1 OF 1	REV A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1827229-6](#)