



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
J	—		E1	REVISED PER ECR-10-019980	04OCT10	HMR
						TM

TABLE


②	ヘッダーハウジング (HEADER HOUSING)	6/6ナイロンガラス強化 (6/6 NYLON GRASS FILLED)
①	ポストコンタクト (POST CONTACT)	錫めっき仕上げ 銅合金 (COPPER ALLOY TIN PLATED)
NO.	名称(NAME)	材料(MATERIAL)

- 注)
- 取付穴寸法
 - 適応基板厚：1.6t
 - かん合相手製品型番：
プラグハウジング：SEE TABLE


- NOTES)
- RECOMMENDED P.C.B LAY OUT
 - APPLICABLE P.C.B. THICKNESS:1.6
 - MATING CONN. P/N
PLUG HOUSING :SEE TABLE




TYPE OF KEYING



PCB. LAYOUT ON RECOMMENDATION



パンチ加工 (PUNCHED HOLE)	0.7 ^{+0.1} ₋₀
ドリル加工 (DRILLED HOLE)	0.8±0.05
	A 寸法 DIM. A



*-1827387-3	WITHOUT	TYPE C	BLUE	7-1827393-3
*-1827387-1	WITHOUT	TYPE A	NATURAL	5-1827393-1
*-1827387-3	WITH	TYPE C	BLUE	2-1827393-3
*-1827387-1	WITH	TYPE A	NATURAL	1827393-1
MATING CONN. P/N 	KINK	TYPE OF KEYING	COLOR	PART NUMBER

KINK FORM

× CHARACTER S IS STRAIGHT PIN.

8 POS	KINK FORM	B	S	S	B
	CIRCUIT NO.	5	6	7	8
	KINK FORM	A	S	S	A
	CIRCUIT NO.	1	2	3	4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位： 耗
mm

MATERIAL
材料
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ± 0.3
1 PLC ± 0.3
2 PLC ± 0.25
3 PLC ± —
4 PLC ± —
ANGLES ± —
FINISH
仕上 —

DWN
T.HATANO
19APR2005

CHK
N.YAMASAKI
19APR2005

APVD
N.YAMASAKI
19APR2005

PRODUCT SPEC
製品規格
108-78231

APPLICATION SPEC
取付適用規格
—

WEIGHT
—

Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME
名称
GRACE INERTIA CONNECTOR 3.3
HEADER ASSEMBLY 8POS

SIZE
A3

CAGE CODE
00779

DRAWING NO
番号
C-1827393

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
尺度 3:1

SHEET
1 OF 1

REV
E1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1827393-1](#)