










THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J	-			SEE SHEET 1 OF 3		









推奨基板取付穴寸法: コネクタ搭載面 (非累積公差)
PC基板厚: 1.0~1.6±0.1
RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

ONLY 4POS




SCALE 2:1

4POS(X-KEY):1-1827875-2












6POS(X-KEY):1-1827875-3

8POS(X-KEY):1-1827875-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. KUDO	14JAN2005	 TE Connectivity	
		CHK D. MITSUGI	14JAN2005		
DIMENSIONS: mm		APVD D. MITSUGI	14JAN2005	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) 4-20POS	
		PRODUCT SPEC 108-78268			
		APPLICATION SPEC 114-5377			
		WEIGHT -			
		CUSTOMER DRAWING			
		SCALE 4:1			
MATERIAL &material		FINISH -		RESTRICTED TO -	
				SHEET 2 OF 3	
				REV B	



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J	-			SEE SHEET 1 OF 3		



10POS(X-KEY):1-1827875-5

12POS(X-KEY):1-1827875-6

16POS(X-KEY):1-1827875-8

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. KUDO	14JAN2005	 TE Connectivity							
DIMENSIONS: mm		CHK D. MITSUGI	14JAN2005								
 		APVD D. MITSUGI	14JAN2005	NAME DYNAMIC DI200D 2.5mmPITCH HDR ASSY (V-TYPE) 4-20POS							
		PRODUCT SPEC 108-78268									
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±0.0001		APPLICATION SPEC 114-5377		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO -				
		WEIGHT -		A300779	C=1827875						
MATERIAL &material		FINISH -		CUSTOMER DRAWING				SCALE 4:1	SHEET 3	OF 3	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1827875-5](#)