

LOC	DIST	REVISIONS					
E	B	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	ECR-07-011430	14/05/07	AM	FWK

NOTES:

1. ELECTRICAL DATA:
- CONTACT RESISTANCE:

INSULATION RESISTANCE:

CURRENT RATING:

BREAKDOWN VOLTAGE:
- 10 mOhm MAX

100 MOhm MIN at 500VDC

5 AMPS


500 VAC MIN PER MINUTE
2. ENVIRONMENTAL:
- OPERATING TEMPERATURE:

SEALING REQUIREMENTS:
- 25°C TO +90°C



IP67
3. PROD SPEC:
- 108-3641
4. PACKAGING:
- 107-3334
5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

ITEM	DESCRIPTION	MATERIAL	FINISH/COLOUR	QTY
1	SCREW NUT	ZINC DIE CAST	2.5µm NICKEL PLATED	1
2	CONNECTOR BODY	POLYURETHANE	BLACK	1
3	PIN CONTACT	BRASS	0.15µm GOLD PLATED OVER NICKEL	3
4	3 CORE CABLE (CORES 0.34 mm ²)	PU JACKET	BLACK	1

PIN ASSIGNMENTS
FRONT VIEW




4	BLACK
3	BLUE
1	BROWN
PIN	WIRE COLOUR



10000	500 mm	M12 STRAIGHT MALE CONNECTOR 10.0m CABLE	1838237-5
7000	350 mm	M12 STRAIGHT MALE CONNECTOR 7.0m CABLE	1838237-4
5000	250 mm	M12 STRAIGHT MALE CONNECTOR 5.0m CABLE	1838237-3
3000	150 mm	M12 STRAIGHT MALE CONNECTOR 3.0m CABLE	1838237-2
2000	100 mm	M12 STRAIGHT MALE CONNECTOR 2.0m CABLE	1838237-1
DIM A	TOL 'B'	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL

-

DWN
H M RAGHAVENDRA

CHK
F.WHEELER-KING

APVD
F.WHEELER-KING

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

22AUG05

07AUG06

07AUG06

tyco
Electronics

Tyco Electronics Corporation

Bideford, UK, EX39 4HE

M12 STRAIGHT MALE CONNECTOR

3 POSITION, PU CABLE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1838237

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1838237-1](#)