

4



3

2


1

| LOC | DIST | REVISIONS | | | | | |
|-----|------|-----------|-----|-------------|------------|-----|------|
| | | P | LTR | DESCRIPTION | DATE | DWN | APVD |
| E | B | | BA | NEW RELEASE | 11JUNE2010 | PT | St.P |

FOR FURTHER INFORMATION SEE DATA SHEET FOR
SERIES HOLCO, AXIAL LEADED PRECISION RESISTORS



RoHS Compliant



| | | | | | | | | |
|--|--|----------------------------------|--|---|--------------------|-------------------------|--------------------|-----------|
| THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. | | DWN PARUSURAM.T 11JUNE2010 | | <div><div><div></div></div><div>Tyco Electronics</div></div> <div>Tyco Electronics Corporation Dorcan, Swindon, SN3 5HH</div> | | | | |
| DIMENSIONS: mm | | CHK ALLAN.P 11JUNE2010 | | | | | | |
| | | APVD STEPHEN.P 11JUNE2010 | | NAME AXIAL LEADED PRECISION RESISTORS SERIES HOLCO H8 | | | | |
| | | PRODUCT SPEC - | | | | | | |
| | | APPLICATION SPEC - | | | | | | |
| | | WEIGHT - | | | | | | |
| | | CUSTOMER DRAWING | | | | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | | | SIZE A 3 | CAGE CODE 00779 | DRAWING NO C=1879631 | RESTRICTED TO - | |
| 0 PLC ± 0.2 1 PLC ± 0.1 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 5° | | | | SCALE 10:1 | | | SHEET 1 OF 1 | REV BA |
| MATERIAL - | | FINISH - | | | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-1879631-0](#)