

4

3



2

1


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	2009
© COPYRIGHT 2009 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.			


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		BA	NEW RELEASE	09JUNE2010	PT	St.P

FOR FURTHER INFORMATION SEE DATA SHEET FOR
SERIES HOLCO, AXIAL LEADED PRECISION RESISTORS



RoHS Compliant



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN PARUSURAM.T 09JUNE2010	 Tyco Electronics Corporation Dorcan, Swindon, SN3 5HH			
DIMENSIONS: mm		CHK ALLAN.P 09JUNE2010				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD STEPHEN.P 09JUNE2010	NAME AXIAL LEADED PRECISION RESISTORS SERIES HOLCO H8		
	0 PLC ± 0.2		PRODUCT SPEC			
	1 PLC ± 0.1		APPLICATION SPEC			
	2 PLC ± -		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-1879654
3 PLC ± -		CUSTOMER DRAWING		SCALE 10:1	SHEET 1	OF 1
4 PLC ± -				RESTRICTED TO		
ANGLES ± 5°				REV BA		
FINISH -						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1879654-4](#)