




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT -

ALL RIGHTS RESERVED.


REFERENCE MATING INTERFACE PATTERN:
1,27 STAGGERED PITCH x 1,5 ROW-DISTANCE.



SCALE 3:1



SOLDER DETAIL
SCALE 10:1





EXAMPLE SOLDER JOINT

NOTES:

- 1 TAPE FOR VACUUM P&P ONLY FOR DASHNUMBERS 7- /8- /9-
- 2 FOR PACKAGING SEE SHEET 2 OF 2
- 3 WITHOUT VACUUM TAPE.
- 4 CORING-OUTS FOR MANUFACTURING PURPOSE ONLY.
SHAPE MAY VARY, BUT IS NOT FUNCTIONAL FOR THE APPLICATION.
- 5 SHOWN IS A 10 POSITION CONNECTOR.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S4	PACKAGING BLISTER MATERIAL CHANGE	08MAY2015	NV	PS

PART NUMBER VAC. TAPE. 1	PART REV	PART NUMBER 3	PART REV	NR.OF POS. "n"	"A"	"B" MAX.
7-188275-4	U	0-188275-4	U	4	3,81	7,1
7-188275-6	U	0-188275-6	U	6	6,35	9,7
7-188275-8	U	0-188275-8	U	8	8,89	12,2
8-188275-0	U	1-188275-0	U	10	11,43	14,7
8-188275-2	U	1-188275-2	U	12	13,97	17,3
8-188275-4	U	1-188275-4	U	14	16,51	19,8
8-188275-6	U	1-188275-6	U	16	19,05	22,4
8-188275-8	V	1-188275-8	V	18	21,59	24,9
9-188275-0	U	2-188275-0	U	20	24,13	27,5



POLARIZATION-SLOT
ON THIS SIDE.

ITEM NO.	COMPONENT DESCRIPTION	MATERIAL	FINISH / COLOR
3	PICK & PLACE TAPE	KAPTON	AMBER TRANSPARENT
2	FEMALE HOUSING	POLYAMIDE 4/6,GF	RED
1	FEMALE CONTACT	PHOSPHOR BRONZE	TIN OVER NICKEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. GOSSELINK	TE TE Connectivity CONNECTOR, FEMALE-ON-BOARD TOP-ENTRY, SMD, Micro-MaTch			
DIMENSIONS: mm		CHK -				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -				
PRODUCT SPEC 108-19052		APVD -				
APPLICATION SPEC 114-13318		APVD -				
WEIGHT -		APVD -				
CUSTOMER DRAWING		APVD -				
SCALE 5:1		APVD -				
SHEET 1 OF 2		APVD -				
REV S4		APVD -				

RECOMMENDED PC-BOARD
PAD-LAYOUT TOP VIEW

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm










TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm



7-188275-4

7-188275-6

7-188275-8

8-188275-0

4 POSITION

6 POSITION

8 POSITION

10 POSITION

0-188275-4

0-188275-6

0-188275-8

1-188275-0

8-188275-2

8-188275-4

8-188275-6

8-188275-8

9-188275-0

12 POSITION

14 POSITION

16 POSITION

18 POSITION

20 POSITION










1-188275-2

1-188275-4

1-188275-6

1-188275-8

2-188275-0



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

M. GOSSELINK

CHK

-

APVD

-

PRODUCT SPEC

108-19052

APPLICATION SPEC

114-13318


WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±-

1 PLC

±0.1

2 PLC

±0.05

3 PLC

±-

4 PLC

±-

ANGLES

±-

FINISH

-

MATERIAL

-



TE Connectivity

CONNECTOR,
FEMALE-ON-BOARD TOP-ENTRY,
SMD, Micro-MaTch

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-188275

-

SCALE

1:1

SHEET

2

OF

2

REV

S4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-188275-8](#)